



UniSpot

BVP375 1LED RGB 24V 30 DMX 10W

UniSpot, 210 lm, 10 W, Red, green and blue, DMX, Safety class III

Philips UniSpot features a sophisticated and compact design that balances beauty and functionality, unobtrusively blending into diverse urban applications. Spotlights in the UniSpot range feature a cylindrical geometry separated into two sections. The front section provides illumination, while the back section connects to heating or other systems using a variety of accessories. Two indication plates on the stand and base make the installation process simple and easy.

Product data

General Information		Controls and Dimming	
Driver included	No	Dimmable	Yes
		Control interface	DMX
Light Technical		Mechanical and Housing	
Luminous Flux	210 lm	Housing Material	Aluminum Alloy
Correlated Color Temperature (Nom)	-	Optical cover material	Glass
Luminous Efficacy (rated) (Nom)	21 lm/W	Housing Color	Dark gray
Color rendering index (CRI)	>80	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Light source color	Red, green and blue	Mech. impact protection code	IK06 [1 J]
Operating and Electrical		Optical cover type	Clear glass
Input Voltage	24 V	Net Weight (Piece)	0.500 kg
Line Frequency	- Hz	Approval and Application	
Power Consumption	10 W	CE mark	Yes
Power Factor (Fraction)	-	Ambient temperature range	-40 to +50 °C
Connection	2 Push-in connector 5-pole	Initial Performance (IEC Compliant)	
Cable	2 cables 0.3m with connector 5-pole	Luminous flux tolerance	+/-10%
Protection class IEC	Safety class III		

Power consumption tolerance	+/-10%
Product Data	
Order product name	BVP375 1LED RGB 24V 30 DMX 10W
Full product name	BVP375 1LED RGB 24V 30 DMX 10W
Full product code	872110370242599
Order code	911401734004

Material Nr. (12NC)	911401734004
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103702425
Numerator - Packs per outer box	40
EAN/UPC - Case	8721103702425

Dimensional drawing

