



UniSpot

BVP376 1LED 40K 24V 20 20W COB

UniSpot, 1730 lm, 20 W, 840 neutral white, Safety class III

Philips UniSpot features a sophisticated and compact design that balances beauty and functionality, unobtrusively blending into diverse urban applications. Spotlights in the UniSpot range feature a cylindrical geometry separated into two sections. The front section provides illumination, while the back section connects to heating or other systems using a variety of accessories. Two indication plates on the stand and base make the installation process simple and easy.

Product data

General Information	
Driver included	No

Light Technical	
Luminous Flux	1,730 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	86 lm/W
Color rendering index (CRI)	>80
Light source color	840 neutral white

Operating and Electrical	
Input Voltage	24 V
Line Frequency	- Hz
Power Consumption	20 W
Power Factor (Fraction)	-
Connection	2 Push-in connector 2-pole
Cable	2 cables 0.3m with connector 2-pole
Protection class IEC	Safety class III

Controls and Dimming	
Dimmable	No
Control interface	-

Mechanical and Housing	
Housing Material	Aluminum Alloy
Optical cover material	Glass
Housing Color	Dark gray
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Optical cover type	Clear glass
Net Weight (Piece)	0.839 kg

Approval and Application	
CE mark	Yes
Ambient temperature range	-40 to +50 °C

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Power consumption tolerance	+/-10%
Product Data	
Order product name	BVP376 1LED 40K 24V 20 20W COB
Full product name	BVP376 1LED 40K 24V 20 20W COB
Full product code	872110370245699
Order code	911401734074

Material Nr. (12NC)	911401734074
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103702456
Numerator - Packs per outer box	18
EAN/UPC - Case	8721103702456

Dimensional drawing

