



UniSpot

BVP376 1LED 40K 24V 35 DMX 20W COB

UniSpot, 1695 lm, 20 W, 840 neutral white, DMX, Safety class III

Philips UniSpot features a sophisticated and compact design that balances beauty and functionality, unobtrusively blending into diverse urban applications. Spotlights in the UniSpot range feature a cylindrical geometry separated into two sections. The front section provides illumination, while the back section connects to heating or other systems using a variety of accessories. Two indication plates on the stand and base make the installation process simple and easy.

Product data

General Information		Controls and Dimming	
Driver included	No	Dimmable	Yes
		Control interface	DMX
Light Technical		Mechanical and Housing	
Luminous Flux	1,695 lm	Housing Material	Aluminum Alloy
Correlated Color Temperature (Nom)	4000 K	Optical cover material	Glass
Luminous Efficacy (rated) (Nom)	84 lm/W	Housing Color	Dark gray
Color rendering index (CRI)	>80	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Light source color	840 neutral white	Mech. impact protection code	IK06 [1 J]
		Optical cover type	Clear glass
		Net Weight (Piece)	0.839 kg
Operating and Electrical		Approval and Application	
Input Voltage	24 V	CE mark	Yes
Line Frequency	- Hz	Ambient temperature range	-40 to +50 °C
Power Consumption	20 W		
Power Factor (Fraction)	-	Initial Performance (IEC Compliant)	
Connection	2 Push-in connector 5-pole	Luminous flux tolerance	+/-10%
Cable	2 cables 0.3m with connector 5-pole		
Protection class IEC	Safety class III		

Power consumption tolerance	+/-10%
Product Data	
Order product name	BVP376 1LED 40K 24V 35 DMX 20W COB
Full product name	BVP376 1LED 40K 24V 35 DMX 20W COB
Full product code	872110370255599
Order code	911401734214

Material Nr. (12NC)	911401734214
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103702555
Numerator - Packs per outer box	18
EAN/UPC - Case	8721103702555

Dimensional drawing

