



UniSpot

BVP377 1LED 30K 24V 15 30W COB

UniSpot, 2230 lm, 30 W, 830 warm white, Safety class III

Philips UniSpot features a sophisticated and compact design that balances beauty and functionality, unobtrusively blending into diverse urban applications. Spotlights in the UniSpot range feature a cylindrical geometry separated into two sections. The front section provides illumination, while the back section connects to heating or other systems using a variety of accessories. Two indication plates on the stand and base make the installation process simple and easy.

Product data

General Information		Controls and Dimming	
Driver included	No	Dimmable	No
		Control interface	-
Light Technical		Mechanical and Housing	
Luminous Flux	2,230 lm	Housing Material	Aluminum Alloy
Correlated Color Temperature (Nom)	3000 K	Optical cover material	Glass
Luminous Efficacy (rated) (Nom)	74 lm/W	Housing Color	Dark gray
Color rendering index (CRI)	>80	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Light source color	830 warm white	Mech. impact protection code	IK06 [1 J]
Operating and Electrical		Optical cover type	Clear glass
Input Voltage	24 V	Net Weight (Piece)	1.800 kg
Line Frequency	- Hz	Approval and Application	
Power Consumption	30 W	CE mark	Yes
Power Factor (Fraction)	-	Ambient temperature range	-40 to +50 °C
Connection	2 Push-in connector 2-pole	Initial Performance (IEC Compliant)	
Cable	2 cables 0.3m with connector 2-pole	Luminous flux tolerance	+/-10%
Protection class IEC	Safety class III		

Power consumption tolerance	+/-10%
Product Data	
Order product name	BVP377 1LED 30K 24V 15 30W COB
Full product name	BVP377 1LED 30K 24V 15 30W COB
Full product code	872110370268599
Order code	911401734384

Material Nr. (12NC)	911401734384
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103702685
Numerator - Packs per outer box	8
EAN/UPC - Case	8721103702685

Dimensional drawing

