



UniSpot

BVP377 3LED RGB40K 24V 55 DMX 30W

UniSpot, 975 lm, 30 W, Red, green, blue and white, DMX, Safety class III

Philips UniSpot features a sophisticated and compact design that balances beauty and functionality, unobtrusively blending into diverse urban applications. Spotlights in the UniSpot range feature a cylindrical geometry separated into two sections. The front section provides illumination, while the back section connects to heating or other systems using a variety of accessories. Two indication plates on the stand and base make the installation process simple and easy.

Product data

General Information		Protection class IEC	
Driver included	No	Protection class IEC	Safety class III
Light Technical		Controls and Dimming	
Luminous Flux	975 lm	Dimmable	Yes
Correlated Color Temperature (Nom)	RGBW	Control interface	DMX
Luminous Efficacy (rated) (Nom)	32 lm/W	Mechanical and Housing	
Color rendering index (CRI)	>80	Housing Material	Aluminum Alloy
Light source color	Red, green, blue and white	Optical cover material	Glass
Operating and Electrical		Housing Color	Dark gray
Input Voltage	24 V	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Line Frequency	- Hz	Mech. impact protection code	IK06 [1 J]
Power Consumption	30 W	Optical cover type	Clear glass
Power Factor (Fraction)	-	Net Weight (Piece)	1.800 kg
Connection	2 Push-in connector 5-pole	Approval and Application	
Cable	2 cables 0.3m with connector 5-pole	CE mark	Yes

Ambient temperature range	-40 to +50 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Product Data	
Order product name	BVP377 3LED RGB40K 24V 55 DMX 30W
Full product name	BVP377 3LED RGB40K 24V 55 DMX 30W

Full product code	872110370290699
Order code	911401734644
Material Nr. (12NC)	911401734644
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103702906
Numerator - Packs per outer box	8
EAN/UPC - Case	8721103702906

Dimensional drawing

