



UniStrip G4

BCP381 12LED 30K 24V A2 L50

UniStrip G4, 848 lm, 12 W, Warm white, 16° x 35°, Safety class III, Mounting bracket adjustable

UniStrip G4 is a surface-mounted, exterior-rated LED luminaire that is designed for façade and outdoor architectural lighting applications. One family that fits all your needs, wall washing, grazing and also linear flood lighting. The robust mechanical and unique optical designs make it ideal for illuminating buildings facades, bridges, overpasses and any application that requires a linear lighting solution. Available in white, monochromatic colours, RGB, RGBW and tunable white and DMX control option available with up to 8 pixels (8IDs) to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

Warnings and Safety

- For outdoor use only

Product data

General Information		Operating and Electrical	
Light source replaceable	No	Correlated Color Temperature (Nom)	3000 K
Driver included	No	Luminous Efficacy (rated) (Nom)	71 lm/W
Light source engine type	LED	Color rendering index (CRI)	80
Lighting Technology	LED	Light source color	Warm white
Value ladder	Performance	Luminaire light beam spread	16° x 35°
Serviceability class	Class B, luminaire is equipped with some serviceable parts (when applicable): driver, control units, surge protection device, front cover and mechanical parts	Input Voltage	24 DC V
Light Technical		Line Frequency	- Hz
Luminous Flux	848 lm	Power Consumption	12 W
		Power Factor (Fraction)	1
		Connection	2 Push-in connector 2-pole

UniStrip G4

Cable	2 cables 0.15m with connectors 2-pole
Protection class IEC	Safety class III
Controls and Dimming	
Dimmable	No
Control interface	-
Mechanical and Housing	
Housing Material	Aluminum extruded
Optic material	Polymethyl methacrylate
Optical cover material	Tempered glass
Fixation material	Aluminum
Housing Color	Dark gray
Mounting device	Mounting bracket adjustable
Optical cover finish	Clear
Overall length	500 mm
Overall width	38 mm
Overall height	47 mm
Dimensions (Height x Width x Depth)	47 x 38 x 500 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Optical cover type	Clear flat
Net Weight (Piece)	0.829 kg

Approval and Application	
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
Ambient temperature range	-40 to +50 °C

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	4 SDCM
Power consumption tolerance	+/-10%

Product Data	
Order product name	BCP381 12LED 30K 24V A2 L50
Full product name	BCP381 12LED 30K 24V A2 L50
Full product code	872016972709099
Order code	911401738642
Material Nr. (12NC)	911401738642
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169727090
Numerator - Packs per outer box	15
EAN/UPC - Case	8720169727090

Dimensional drawing

