



UniStrip G4

BCP382 18LED 30K 24V A2 L50

UniStrip G4, 1221 lm, 18 W, Warm white, 16° x 35°, Safety class III, Mounting bracket adjustable

UniStrip G4 is a surface mounted, exterior-rated LED luminaire that is designed for façade and outdoor architectural lighting applications. One family that fits all your needs, wall washing, grazing and also linear flood lighting. The robust mechanical and unique optical designs make it ideal for illuminating buildings facades, bridges, overpasses and any application that requires a linear lighting solution. Available in white, monochromatic colors, RGB, RGBW and tunable white and DMX control option available with up to 8 pixels (8IDs) to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

Warnings and Safety

- For outdoor use only

Product data

General Information		Correlated Color Temperature (Nom) 3000 K	
Light source replaceable	No	Luminous Efficacy (rated) (Nom)	68 lm/W
Driver included	No	Color rendering index (CRI)	80
Light source engine type	LED	Light source color	Warm white
Lighting Technology	LED	Luminaire light beam spread	16° x 35°
Value ladder	Performance	Operating and Electrical	
Serviceability class	Class B, luminaire is equipped with some serviceable parts (when applicable): driver, control units, surge protection device, front cover and mechanical parts	Input Voltage	24 DC V
Light Technical		Line Frequency	- Hz
Luminous Flux	1,221 lm	Power Consumption	18 W
		Power Factor (Fraction)	1
		Connection	2 Push-in connector 2-pole

UniStrip G4

Cable	2 cables 0.15m with connectors 2-pole
Protection class IEC	Safety class III
Controls and Dimming	
Dimmable	No
Control interface	-
Mechanical and Housing	
Housing Material	Aluminum extruded
Optic material	Polymethyl methacrylate
Optical cover material	Tempered glass
Fixation material	Aluminum
Housing Color	Dark gray
Mounting device	Mounting bracket adjustable
Optical cover finish	Clear
Overall length	500 mm
Overall width	38 mm
Overall height	47 mm
Dimensions (Height x Width x Depth)	47 x 38 x 500 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Optical cover type	Clear flat
Net Weight (Piece)	0.899 kg

Approval and Application

Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
Ambient temperature range	-40 to +50 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	4 SDCM
Power consumption tolerance	+/-10%

Product Data

Order product name	BCP382 18LED 30K 24V A2 L50
Full product name	BCP382 18LED 30K 24V A2 L50
Full product code	872016972676599
Order code	911401739182
Material Nr. (12NC)	911401739182
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169726765
Numerator - Packs per outer box	15
EAN/UPC - Case	8720169726765

Dimensional drawing

