



# UniFlood M G2

## BVP353 16LED RGBNW 220V L18 45 DMX

UniFlood M G2, 1565 lm, 30 W, RGBW, Dynamic DMX/RDM, Safety class I

Philips UniFlood M gen2 is a cost-effective, exterior-rated architectural LED floodlight that's designed for façade, landscape and outdoor flood lighting applications. The robust, modular, rectangular design features highly-efficient optics, making it ideal for illuminating everything from multi-storey façades and bridges to landmarks and monuments. This LED floodlight is available in white, monochromatic colors, RGB, RGBW and tunable white. It comes with six different spread lenses ranging from narrow spot to wide flood and has DMX512/RDM control option. A truly modular floodlight that gives architects and designers the freedom to explore a wide range of concepts and designs with no limitations.

### Warnings and Safety

- For outdoor use only.

### Product data

General Information		Effective projected area	
Driver included	Yes		0.029 m <sup>2</sup>
Lighting Technology	LED	Operating and Electrical	
Value ladder	Performance	Input Voltage	220 to 240 V
		Line Frequency	50 to 60 Hz
		Power Consumption	30 W
		Power Factor (Fraction)	0.8
		Connection	Flying leads/wires and 2 Push-in connector 4-pole
Light Technical		Cable	Cable 0.5 m without plug 3-pole and 2 Cables 0.5 m with connector 4-pole
Luminous Flux	1,565 lm		
Correlated Color Temperature (Nom)	-		
Luminous Efficacy (rated) (Nom)	52 lm/W		
Color rendering index (CRI)	>80		
Light source color	RGBW		

# UniFlood M G2

Protection class IEC	Safety class I
<b>Controls and Dimming</b>	
Dimmable	Yes
Control interface	Dynamic DMX/RDM
<b>Mechanical and Housing</b>	
Housing Material	Aluminum extruded
Optical cover material	Acrylate
Housing Color	Dark gray
Overall length	183 mm
Overall width	140 mm
Overall height	149 mm
Dimensions (Height x Width x Depth)	149 x 140 x 183 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Optical cover type	Clear glass
Net Weight (Piece)	2.188 kg
<b>Approval and Application</b>	
Flammability mark	For mounting on normally flammable surfaces

CE mark	Yes
Ambient temperature range	-40 to +50 °C
<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
<b>Product Data</b>	
Order product name	BVP353 16LED RGBNW 220V L18 45 DMX
Full product name	BVP353 16LED RGBNW 220V L18 45 DMX
Full product code	871951492534299
Order code	911401746133
Material Nr. (12NC)	911401746133
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514925342
Numerator - Packs per outer box	8
EAN/UPC - Case	8719514925342

## Dimensional drawing

