



UniFlood M G2

BVP353 24LED 30K 220V L24 30

UniFlood M G2, 4100 lm, 50 W, 830 warm white, Safety class I

Philips UniFlood M gen2 is a cost-effective, exterior-rated architectural LED floodlight that's designed for façade, landscape and outdoor flood lighting applications. The robust, modular, rectangular design features highly-efficient optics, making it ideal for illuminating everything from multi-storey façades and bridges to landmarks and monuments. This LED floodlight is available in white, monochromatic colors, RGB, RGBW and tunable white. It comes with six different spread lenses ranging from narrow spot to wide flood and has DMX512/RDM control option. A truly modular floodlight that gives architects and designers the freedom to explore a wide range of concepts and designs with no limitations.

Warnings and Safety

- For outdoor use only.

Product data

General Information	
Driver included	Yes
Lighting Technology	LED
Value ladder	Performance

Light Technical	
Luminous Flux	4,100 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	82 lm/W
Color rendering index (CRI)	>80
Light source color	830 warm white
Effective projected area	0.038 m ²

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Power Consumption	50 W
Power Factor (Fraction)	0.9
Connection	Flying leads/wires
Cable	Cable without plug 3-pole
Protection class IEC	Safety class I

Controls and Dimming	
Dimmable	No
Control interface	-

UniFlood M G2

Mechanical and Housing

Housing Material	Aluminum extruded
Optical cover material	Acrylate
Housing Color	Dark gray
Overall length	238 mm
Overall width	140 mm
Overall height	149 mm
Dimensions (Height x Width x Depth)	149 x 140 x 238 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Optical cover type	Clear glass
Net Weight (Piece)	3.000 kg

Approval and Application

Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
Ambient temperature range	-40 to +50 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	4 SDCM
Power consumption tolerance	+/-10%

Product Data

Order product name	BVP353 24LED 30K 220V L24 30
Full product name	BVP353 24LED 30K 220V L24 30
Full product code	871951492590899
Order code	911401746693
Material Nr. (12NC)	911401746693
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514925908
Numerator - Packs per outer box	8
EAN/UPC - Case	8719514925908

Dimensional drawing

