



# UniFlood M G2

## BVP354 120LED 30K 220V L50 30

UniFlood M G2, 20500 lm, 240 W, 830 warm white, Safety class I

Philips UniFlood M gen2 is a cost-effective, exterior-rated architectural LED floodlight that's designed for façade, landscape and outdoor flood lighting applications. The robust, modular, rectangular design features highly-efficient optics, making it ideal for illuminating everything from multi-storey façades and bridges to landmarks and monuments. This LED floodlight is available in white, monochromatic colors, RGB, RGBW and tunable white. It comes with six different spread lenses ranging from narrow spot to wide flood and has DMX512/RDM control option. A truly modular floodlight that gives architects and designers the freedom to explore a wide range of concepts and designs with no limitations.

### Warnings and Safety

- For outdoor use only.

### Product data

General Information		Effective projected area	
Driver included	Yes	0.156 m <sup>2</sup>	
Lighting Technology	LED	Operating and Electrical	
Value ladder	Performance	Input Voltage	220 to 240 V
<b>Light Technical</b>		Line Frequency	50 to 60 Hz
Luminous Flux	20,500 lm	Inrush current	60 A
Correlated Color Temperature (Nom)	3000 K	Power Consumption	240 W
Luminous Efficacy (rated) (Nom)	85 lm/W	Power Factor (Fraction)	0.9
Color rendering index (CRI)	>80	Connection	Flying leads/wires
Light source color	830 warm white	Cable	Cable without plug 3-pole

# UniFlood M G2

Protection class IEC	Safety class I
<b>Controls and Dimming</b>	
Dimmable	No
Control interface	-
<b>Mechanical and Housing</b>	
Housing Material	Aluminum extruded
Optical cover material	Acrylate
Housing Color	Dark gray
Overall length	486 mm
Overall width	304 mm
Overall height	231 mm
Dimensions (Height x Width x Depth)	231 x 304 x 486 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Optical cover type	Clear glass
Net Weight (Piece)	13.000 kg
<b>Approval and Application</b>	
Flammability mark	For mounting on normally flammable surfaces

CE mark	Yes
Ambient temperature range	-40 to +50 °C
<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+/-10%
Initial chromaticity	4 SDCM
Power consumption tolerance	+/-10%
<b>Product Data</b>	
Order product name	BVP354 120LED 30K 220V L50 30
Full product name	BVP354 120LED 30K 220V L50 30
Full product code	871951492842800
Order code	911401749213
Material Nr. (12NC)	911401749213
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514928428
Numerator - Packs per outer box	1
EAN/UPC - Case	8719514928428

## Dimensional drawing

