



# UniFlood M G2

## BVP354 120LED RGBNW 220V L50 45 DMX

UniFlood M G2, 11750 lm, 240 W, RGBW, Dynamic DMX/RDM, Safety class I

Philips UniFlood M gen2 is a cost-effective, exterior-rated architectural LED floodlight that's designed for façade, landscape and outdoor flood lighting applications. The robust, modular, rectangular design features highly-efficient optics, making it ideal for illuminating everything from multi-storey façades and bridges to landmarks and monuments. This LED floodlight is available in white, monochromatic colors, RGB, RGBW and tunable white. It comes with six different spread lenses ranging from narrow spot to wide flood and has DMX512/RDM control option. A truly modular floodlight that gives architects and designers the freedom to explore a wide range of concepts and designs with no limitations.

### Warnings and Safety

- For outdoor use only.

### Product data

General Information		Effective projected area	
Driver included	Yes		0.156 m <sup>2</sup>
Lighting Technology	LED	Operating and Electrical	
Value ladder	Performance	Input Voltage	220 to 240 V
		Line Frequency	50 to 60 Hz
		Inrush current	60 A
		Power Consumption	240 W
		Power Factor (Fraction)	0.9
Light Technical		Connection	Flying leads/wires and 2 Push-in connector 4-pole
Luminous Flux	11,750 lm	Cable	Cable 0.5 m without plug 3-pole and 2 Cables 0.5 m with connector 4-pole
Correlated Color Temperature (Nom)	-		
Luminous Efficacy (rated) (Nom)	49 lm/W		
Color rendering index (CRI)	>80		
Light source color	RGBW		

# UniFlood M G2

Protection class IEC	Safety class I
<b>Controls and Dimming</b>	
Dimmable	Yes
Control interface	Dynamic DMX/RDM
<b>Mechanical and Housing</b>	
Housing Material	Aluminum extruded
Optical cover material	Acrylate
Housing Color	Dark gray
Overall length	486 mm
Overall width	304 mm
Overall height	231 mm
Dimensions (Height x Width x Depth)	231 x 304 x 486 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Optical cover type	Clear glass
Net Weight (Piece)	13.000 kg
<b>Approval and Application</b>	
Flammability mark	For mounting on normally flammable surfaces

CE mark	Yes
Ambient temperature range	-40 to +50 °C
<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
<b>Product Data</b>	
Order product name	BVP354 120LED RGBNW 220V L50 45 DMX
Full product name	BVP354 120LED RGBNW 220V L50 45 DMX
Full product code	871951492858900
Order code	911401749373
Material Nr. (12NC)	911401749373
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514928589
Numerator - Packs per outer box	1
EAN/UPC - Case	8719514928589

## Dimensional drawing

