



UniFlood M G2

BVP354 144LED 40K 220V L57 30

UniFlood M G2, 28810 lm, 300 W, 840 neutral white, Safety class I

The Philips UniFlood M gen2 is a cost-effective, exterior-rated architectural LED floodlight that's designed for façade, landscape and outdoor floodlighting applications. The robust, modular, rectangular design features highly-efficient optics, making it ideal for illuminating everything from multi-storey façades and bridges to landmarks and monuments. This LED floodlight is available in white, monochromatic colours, RGB, RGBW and tunable white. It comes with six different spread lenses ranging from narrow spot to wide flood and has DMX512/RDM control option. A truly modular floodlight that gives architects and designers the freedom to explore a wide range of concepts and designs with no limitations.

Warnings and Safety

- For outdoor use only.

Product data

General Information		Effective projected area	0.182 m ²
Driver included	Yes	Operating and Electrical	
Lighting Technology	LED	Input Voltage	220 to 240 V
Value ladder	Performance	Line Frequency	50 to 60 Hz
Light Technical		Inrush current	60 A
Luminous Flux	28,810 lm	Power Consumption	300 W
Correlated Colour Temperature (Nom)	4000 K	Power Factor (Fraction)	0.95
Luminous efficacy (rated) (nom.)	96 lm/W	Connection	Flying leads/cables
Colour rendering index (CRI)	>80	Cable	Cable without plug 3-pole
Light source colour	840 neutral white		

UniFlood M G2

Protection class IEC	Safety class I
Controls and Dimming	
Dimmable	No
Control interface	-
Mechanical and Housing	
Housing material	Extruded aluminium
Optical cover/lens material	Acrylate
Housing Colour	Dark grey
Overall length	569 mm
Overall width	304 mm
Overall height	231 mm
Dimensions (height x width x depth)	231 x 304 x 569 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Optical cover type	Clear glass
Net Weight (Piece)	14.000 kg
Approval and Application	
Flammability mark	For mounting on normally flammable surfaces

CE mark	Yes
Ambient temperature range	-40 to +50 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	4 SDCM
Power consumption tolerance	+/-10%
Product Data	
Order product name	BVP354 144LED 40K 220V L57 30
Full product name	BVP354 144LED 40K 220V L57 30
Full EOC	871951492879400
Order code	911401749583
Material no. (12 NC)	911401749583
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514928794
Numerator – packs per outer box	1
EAN/UPC - Case	8719514928794

Dimensional drawing

