



UniFlood C Pro

BVP372 16LED 27K 220V 10 40W HP

UniFlood C Pro, 2465 lm, 40 W, 827 warm white, Safety class I

Philips UniFlood C Pro offers a unique rugged elegance, with a cylindrical form and flowing lines that connect the front and back housings beautifully. This is compact architectural floodlighting design where every element has a purpose; the front section provides exceptional lighting, while the back section houses all the electrical components. Between the two, the fins dissipate heat and also serve as a decorative element. Exterior-rated, Philips UniFlood C Pro is a cost-effective, architectural LED floodlight that is designed for façade, landscape and outdoor floodlighting applications. The robust mechanical design and high-efficiency optics make it ideal for illuminating multi-story exterior façades, bridges, landmarks and monuments. Architects and designers have the freedom to explore a wide range of concepts and designs with no limitations, thanks to a range of colors, multiple spread lenses and a DMX512/RDM control option.

Warnings and Safety

- For outdoor use only

Product data

General Information	
Color Code	827 warm white
Driver included	Yes
Lighting Technology	LED
Value ladder	Performance

Light Technical	
Luminous Flux	2,465 lm
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	62 lm/W

Color rendering index (CRI)	>80
Light source color	827 warm white

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Power Consumption	40 W
Power Factor (Fraction)	0.9
Connection	Flying leads/wires
Cable	Cable 0.5 m without plug 3-pole

UniFlood C Pro

Protection class IEC	Safety class I
----------------------	----------------

Controls and Dimming

Dimmable	No
Control interface	-

Mechanical and Housing

Housing Material	Aluminum die cast
Optical cover material	Polycarbonate
Housing Color	Dark gray
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Optical cover type	Clear glass
Net Weight (Piece)	3.000 kg

Approval and Application

CE mark	Yes
Ambient temperature range	-40 to +50 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	BVP372 16LED 27K 220V 10 40W HP
Full product name	BVP372 16LED 27K 220V 10 40W HP
Full product code	872016950392299
Order code	911401774103
Material Nr. (12NC)	911401774103
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169503922
Numerator - Packs per outer box	4
EAN/UPC - Case	8720169503922

Dimensional drawing

