



UniFlood C Pro

BVP372 16LED RGBW 220V 10 DMX 40W HP

UniFlood C Pro, 1580 lm, 40 W, RGBW, Dynamic DMX/RDM, Safety class I

Philips UniFlood C Pro offers a unique rugged elegance, with a cylindrical form and flowing lines that connect the front and back housings beautifully. This is compact architectural floodlighting design where every element has a purpose; the front section provides exceptional lighting, while the back section houses all the electrical components. Between the two, the fins dissipate heat and also serve as a decorative element. Exterior-rated, Philips UniFlood C Pro is a cost-effective, architectural LED floodlight that is designed for façade, landscape and outdoor floodlighting applications. The robust mechanical design and high-efficiency optics make it ideal for illuminating multi-story exterior façades, bridges, landmarks and monuments. Architects and designers have the freedom to explore a wide range of concepts and designs with no limitations, thanks to a range of colors, multiple spread lenses and a DMX512/RDM control option.

Warnings and Safety

- For outdoor use only

Product data

General Information		Operating and Electrical	
Color Code	RGBW	Luminous Efficacy (rated) (Nom)	40 lm/W
Driver included	Yes	Color rendering index (CRI)	N.A.
Lighting Technology	LED	Light source color	RGBW
Value ladder	Performance		
Light Technical		Input Voltage	220 to 240 V
Luminous Flux	1,580 lm	Line Frequency	50 to 60 Hz
Correlated Color Temperature (Nom)	-	Power Consumption	40 W
		Power Factor (Fraction)	0.9

UniFlood C Pro

Connection	Flying leads/wires and 2 Push-in connector 4-pole
Cable	Cable 0.5 m without plug 3-pole and 2 Cables 0.5 m with connector 4-pole
Protection class IEC	Safety class I
Controls and Dimming	
Dimmable	Yes
Control interface	Dynamic DMX/RDM
Mechanical and Housing	
Housing Material	Aluminum die cast
Optical cover material	Polycarbonate
Housing Color	Dark gray
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Optical cover type	Clear glass
Net Weight (Piece)	3.000 kg
Approval and Application	
CE mark	Yes

Ambient temperature range	-40 to +50 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Product Data	
Order product name	BVP372 16LED RGBNW 220V 10 DMX 40W HP
Full product name	BVP372 16LED RGBNW 220V 10 DMX 40W HP
Full product code	872016950422699
Order code	911401774403
Material Nr. (12NC)	911401774403
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169504226
Numerator - Packs per outer box	4
EAN/UPC - Case	8720169504226

Dimensional drawing

