



UniFlood C Pro

BVP373 30LED RGB 220V 10 DMX 80W HP

UniFlood C Pro, 2695 lm, 80 W, RGB, Dynamic DMX/RDM, Safety class I

Philips UniFlood C Pro offers a unique rugged elegance, with a cylindrical form and flowing lines that connect the front and back housings beautifully. This is compact architectural floodlighting design where every element has a purpose; the front section provides exceptional lighting, while the back section houses all the electrical components. Between the two, the fins dissipate heat and also serve as a decorative element. Exterior-rated, Philips UniFlood C Pro is a cost-effective, architectural LED floodlight that is designed for façade, landscape and outdoor floodlighting applications. The robust mechanical design and high-efficiency optics make it ideal for illuminating multi-story exterior façades, bridges, landmarks and monuments. Architects and designers have the freedom to explore a wide range of concepts and designs with no limitations, thanks to a range of colors, multiple spread lenses and a DMX512/RDM control option.

Warnings and Safety

- For outdoor use only

Product data

General Information		Luminous Efficacy (rated) (Nom)	
Color Code	RGB		34 lm/W
Driver included	Yes	Color rendering index (CRI)	N.A.
Lighting Technology	LED	Light source color	RGB
Value ladder	Performance		
Light Technical		Operating and Electrical	
Luminous Flux	2,695 lm	Input Voltage	220 to 240 V
Correlated Color Temperature (Nom) -		Line Frequency	50 to 60 Hz
		Power Consumption	80 W
		Power Factor (Fraction)	0.9

UniFlood C Pro

Connection	Flying leads/wires and 2 Push-in connector 4-pole
Cable	Cable 0.5 m without plug 3-pole and 2 Cables 0.5 m with connector 4-pole
Protection class IEC	Safety class I
Controls and Dimming	
Dimmable	Yes
Control interface	Dynamic DMX/RDM
Mechanical and Housing	
Housing Material	Aluminum die cast
Optical cover material	Polycarbonate
Housing Color	Dark gray
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Optical cover type	Clear glass
Net Weight (Piece)	6.000 kg
Approval and Application	
CE mark	Yes

Ambient temperature range	-40 to +50 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Product Data	
Order product name	BVP373 30LED RGB 220V 10 DMX 80W HP
Full product name	BVP373 30LED RGB 220V 10 DMX 80W HP
Full product code	872016950507099
Order code	911401775253
Material Nr. (12NC)	911401775253
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169505070
Numerator - Packs per outer box	2
EAN/UPC - Case	8720169505070

Dimensional drawing

