



# UniFlood C Pro

## BVP374 48LED RGB 220V 10 DMX 120W HP

UniFlood C Pro, 4035 lm, 120 W, RGB, Dynamic DMX/RDM, Safety class I

Philips UniFlood C Pro offers a unique rugged elegance, with a cylindrical form and flowing lines that connect the front and back housings beautifully. This is compact architectural floodlighting design where every element has a purpose; the front section provides exceptional lighting, while the back section houses all the electrical components. Between the two, the fins dissipate heat and also serve as a decorative element. Exterior-rated, Philips UniFlood C Pro is a cost-effective, architectural LED floodlight that is designed for façade, landscape and outdoor floodlighting applications. The robust mechanical design and high-efficiency optics make it ideal for illuminating multi-story exterior façades, bridges, landmarks and monuments. Architects and designers have the freedom to explore a wide range of concepts and designs with no limitations, thanks to a range of colors, multiple spread lenses and a DMX512/RDM control option.

### Warnings and Safety

- For outdoor use only

### Product data

General Information	
Color Code	RGB
Driver included	Yes
Lighting Technology	LED
Value ladder	Performance
Light Technical	
Luminous Flux	4,035 lm
Correlated Color Temperature (Nom)	-

Luminous Efficacy (rated) (Nom)	34 lm/W
Color rendering index (CRI)	N.A.
Light source color	RGB
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Power Consumption	120 W
Power Factor (Fraction)	0.9

# UniFlood C Pro

<b>Connection</b>	Flying leads/wires and 2 Push-in connector 4-pole
<b>Cable</b>	Cable 0.5 m without plug 3-pole and 2 Cables 0.5 m with connector 4-pole
<b>Protection class IEC</b>	Safety class I
<b>Controls and Dimming</b>	
<b>Dimmable</b>	Yes
<b>Control interface</b>	Dynamic DMX/RDM
<b>Mechanical and Housing</b>	
<b>Housing Material</b>	Aluminum die cast
<b>Optical cover material</b>	Polycarbonate
<b>Housing Color</b>	Dark gray
<b>Ingress protection code</b>	IP66 [Dust penetration-protected, jet-proof]
<b>Mech. impact protection code</b>	IK06 [1 J]
<b>Optical cover type</b>	Clear glass
<b>Net Weight (Piece)</b>	8.000 kg
<b>Approval and Application</b>	
<b>CE mark</b>	Yes

<b>Ambient temperature range</b>	-40 to +50 °C
<b>Initial Performance (IEC Compliant)</b>	
<b>Luminous flux tolerance</b>	+/-10%
<b>Power consumption tolerance</b>	+/-10%
<b>Product Data</b>	
<b>Order product name</b>	BVP374 48LED RGB 220V 10 DMX 120W HP
<b>Full product name</b>	BVP374 48LED RGB 220V 10 DMX 120W HP
<b>Full product code</b>	872016950597199
<b>Order code</b>	911401776153
<b>Material Nr. (12NC)</b>	911401776153
<b>Numerator - Quantity Per Pack</b>	1
<b>EAN/UPC - Product/Case</b>	8720169505971
<b>Numerator - Packs per outer box</b>	2
<b>EAN/UPC - Case</b>	8720169505971

## Dimensional drawing

