



UniFlood C Pro

BVP374 60LED 40K 220V 15 150W HP

UniFlood C Pro, 11430 lm, 150 W, 840 neutral white, Safety class I

The Philips UniFlood C Pro offers a unique rugged elegance, with a cylindrical form and flowing lines that connect the front and back housings beautifully. This is a compact architectural floodlighting design where every element has a purpose; the front section provides exceptional lighting, the back section houses all the electrical components. Between the two, the fins dissipate heat and also serve as a decorative element. Exterior-rated, the Philips UniFlood C Pro is a cost-effective, architectural LED floodlight that is designed for façade, landscape and outdoor floodlighting applications. The robust mechanical design and high-efficiency optics make it ideal for illuminating multi-storey exterior façades, bridges, landmarks and monuments. Architects and designers have the freedom to explore a wide range of concepts and designs with no limitations, thanks to a range of colours, multiple spread lenses and a DMX512/RDM control option.

Warnings and Safety

- For outdoor use only

Product data

General Information		Operating and Electrical	
Color Code	840 neutral white	Luminous efficacy (rated) (nom.)	76 lm/W
Driver included	Yes	Colour rendering index (CRI)	>80
Lighting Technology	LED	Light source colour	840 neutral white
Value ladder	Performance	Input Voltage	220 to 240 V
Light Technical		Line Frequency	50 to 60 Hz
Luminous Flux	11,430 lm	Power Consumption	150 W
Correlated Colour Temperature (Nom)	4000 K	Power Factor (Fraction)	0.9

UniFlood C Pro

Connection	Flying leads/cables
Cable	Cable 0.5 m without plug 3-pole
Protection class IEC	Safety class I
Controls and Dimming	
Dimmable	No
Control interface	-
Mechanical and Housing	
Housing material	Aluminium die cast
Optical cover/lens material	Polycarbonate
Housing Colour	Dark grey
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Optical cover type	Clear glass
Net Weight (Piece)	8.000 kg
Approval and Application	
CE mark	Yes

Ambient temperature range	-40 to +50 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Product Data	
Order product name	BVP374 60LED 40K 220V 15 150W HP
Full product name	BVP374 60LED 40K 220V 15 150W HP
Full EOC	872016950634399
Order code	911401776523
Material no. (12 NC)	911401776523
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8720169506343
Numerator – packs per outer box	2
EAN/UPC - Case	8720169506343

Dimensional drawing

