

BN126Z SC

911401776802



CoreLine Batten, Accessory, IP20 | Finger-protected, IK04 | 0.5 J standard plus, Steel

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Batten range of LED products can be used to replace traditional battens with fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress and as such we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips/Signify cannot guarantee safe failure and product warranty will become void

General Information

Value ladder	Performance
--------------	-------------

Operating and Electrical

Input Voltage	- V
Line Frequency	- Hz
Protection class IEC	Safety class I

Mechanical and Housing

Overall length	57 mm
Overall width	22 mm
Overall height	1,000 mm
Dimensions (height x width x depth)	1000 x 22 x 57 mm
Material	Steel
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK04 [0.5 J standard plus]
Accessory colour	Steel
Net Weight (Piece)	0.064 kg

Related Documents

Documents and certificates	Document Name	Download
Installation Instructions	BN126C-Mounting Instruction-EUR-V1,0-2019-12-19-FINAL v2.pdf	Download 
Tender text	Tender_Text_911401776802_en_GB.txt	Download 

Approval and Application

CE mark	Yes
EU RoHS compliant	Yes

Product Data

Order product name	BN126Z SC
Full product name	BN126Z SC
Full EOC	871016336574999
Order code	911401776802
Material no. (12 NC)	911401776802
Numerator – quantity per pack	1
EAN/UPC — Product/Case	8710163365749
Numerator – packs per outer box	108
EAN/UPC - Case	8710163365831

