



Uni Posttop Classic

BDP400 LED WW 220V 30W TS PSU 9005

Uni Posttop Classic, 3600 lm, 30 W, 730 warm white, Safety class I

Inspired by the well-known street lanterns in 20th Century, the Philips Uni Posttop classic mixes the conventional classic with Philips's modern design, meeting various criteria in quality and safety while providing outstanding lumen performance under the standard of street lighting. The classical housing creates a contemporary feel which fits not only traditional settings but also modern environments. In addition, to cater for different needs in application scenarios, Philips Uni Posttop provides two optics option, i.e., symmetric and asymmetric. Besides, the Philips Uni Posttop classic features a NEMA socket in option, which enables this fixture ready for smart system based on 1-10V or Dali 2.0 interface.

Product data

General Information		Operating and Electrical	
Driver included	Yes	Input Voltage	220 to 240 V
Light source engine type	LED	Line Frequency	50 or 60 Hz
Value ladder	Performance	Power Consumption	30 W
Warranty period	3 years	Power Factor (Fraction)	0.9
Light Technical		Connection	-
Luminous Flux	3,600 lm	Cable	Cable without plug 3-pole
Correlated Color Temperature (Nom)	3000 K	Protection class IEC	Safety class I
Luminous Efficacy (rated) (Nom)	120 lm/W	Controls and Dimming	
Color rendering index (CRI)	70	Dimmable	No
Light source color	730 warm white	Control interface	-
Effective projected area	0.18 m ²		

Uni Posttop Classic

Mechanical and Housing

Housing Material	Aluminum die-cast
Optical cover material	Polycarbonate
Housing Color	Black
Overall length	425 mm
Overall width	425 mm
Overall height	827 mm
Dimensions (Height x Width x Depth)	827 x 425 x 425 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Optical cover type	Clear dome
Net Weight (Piece)	9.300 kg

Approval and Application

Flammability mark	-
CE mark	Yes

Ambient temperature range	-35 °C to 50 °C
---------------------------	-----------------

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	5
Power consumption tolerance	+/-10%

Product Data

Order product name	BDP400 LED WW 220V 30W TS PSU 9005
Full product name	BDP400 LED WW 220V 30W TS PSU 9005
Order code	911401799853
Material Nr. (12NC)	911401799853
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

