



# Essential SmartBright G5 LED Floodlight

## BVP150 LED20/WW PSU 20W SWB MDU G3 GM

Essential SmartBright G5 LED Floodlight, 1880 lm, 20 W, 830 warm white, 110°, Safety class I, Mounting bracket

The Essential SmartBright G5 LED Floodlight is the new successor with robust die-cast aluminum housing suitable for general outdoor application. Lightweight, with a robust die-cast aluminum housing and corrosion-proof coating, it's suitable for general outdoor applications. Plus, with a higher efficacy than the previous generation, it also saves more energy.

### Product data

General Information		Optic type	
Number of gear units	1 unit	Optic type	Wide beam
Gear	-	Luminaire light beam spread	110°
Driver included	Yes	Effective projected area	0.01 m <sup>2</sup>
Light source engine type	LED	Operating and Electrical	
Value ladder	Value	Input Voltage	220 to 240 V
Warranty period	2 years	Line Frequency	50 or 60 Hz
Light Technical		Inrush current	2 A
Luminous Flux	1,880 lm	Inrush time	0.03 ms
Correlated Color Temperature (Nom)	3000 K	Power Consumption	20 W
Luminous Efficacy (rated) (Nom)	94 lm/W	Power Factor (Fraction)	0.9
Color rendering index (CRI)	80	Connection	Flying leads/wires
Number of light sources	1	Cable	Cable 0.3 m without plug
Beam angle of light source	110 degree(s)	Number of products on MCB of 16 A type B	104
Light source color	830 warm white	Suitable for random switching	No

# Essential SmartBright G5 LED Floodlight

Protection class IEC	Safety class I
----------------------	----------------

## Controls and Dimming

Dimmable	No
Control interface	-
Maximum dim level	Not applicable

## Mechanical and Housing

Housing Material	Aluminum die-cast
Reflector material	Polycarbonate
Optic material	Glass
Optical cover material	Glass
Housing Color	Black
Mounting device	Mounting bracket
Optical cover finish	Clear
Overall length	138 mm
Overall width	164 mm
Overall height	56 mm
Dimensions (Height x Width x Depth)	56 x 164 x 138 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Optical cover type	Tempered glass
Net Weight (Piece)	0.350 kg

## Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces

CE mark	No
ENEC mark	-
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
Photobiological risk specification	0.2 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-40 to +50 °C


## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.44, 0.40) SDCM≤6
Power consumption tolerance	+/-10%

## Product Data

Order product name	BVP150 LED20/WW PSU 20W SWB MDU G3 GM
Full product name	BVP150 LED20/WW PSU 20W SWB MDU G3 GM
Full product code	872016952174299
Order code	911401801586
Material Nr. (12NC)	911401801586
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169521742
Numerator - Packs per outer box	36
EAN/UPC - Case	8720169521827

## Dimensional drawing



# Essential SmartBright G5 LED Floodlight

