



# CoreLine Panel gen6

## RC132V G6 43S/840 WIA W60L60 OC

CoreLine Panel gen6, 31 W, 600x600 mm, VPC, 4300 lm, 4000 K, Wireless, Interact Ready

Philips CoreLine panel Gen6 delivers on the CoreLine promise of innovation, easy installation, and excellent illumination. Designed as a direct replacement for functional luminaires in general lighting applications, this LED panel light's innovative All-in feature offers a choice of three lumen packages and three-color temperatures in a single luminaire. This makes it easy to select the right product, gives you the flexibility respond to customer preferences on site, and means fewer product codes on stock. Installing the CoreLine RC132V LED panel is quick and easy, using the product's quick connector or flywire. The CoreLine range includes Interact Ready luminaires with integrated wireless communications, ready to be used with Interact gateways, sensors, and software.

### Product data

General Information		Operating and Electrical	
Number of gear units	1 unit	Luminous Efficacy (rated) (Nom)	140 lm/W
Driver included	Yes	Color rendering index (CRI)	>80
Service tag	Yes	Beam angle of light source	90 degree(s)
Value ladder	Performance	Light source color	840 neutral white
Serviceability class	Class C, luminaire without serviceable parts, not serviceable	Optic type	Beam angle 90°
Warranty period	5 years	Luminaire light beam spread	90°
Sustainability rating	Unclassified	Unified glare rating CEN	19
Light Technical		Operating and Electrical	
Luminous Flux	4,300 lm	Input Voltage	220 to 240 V
Correlated Color Temperature (Nom)	4000 K	Line Frequency	50 or 60 Hz
		Inrush current	4.8 A
		Inrush time	0.056 ms

## CoreLine Panel gen6

Power Consumption	31 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 2-pole
Cable	-
Number of products on MCB of 16 A type B	50
Suitable for random switching	Not applicable
Protection class IEC	Safety class II
Total harmonic distortion	20 %

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Wireless driver Interact System ready
Control interface	Wireless
Constant light output	No
Maximum dim level	1%
Connectivity	Interact Ready

### Mechanical and Housing

Housing Material	Steel
Reflector material	Acrylate
Optic material	Polystyrene
Optical cover material	Polystyrene
Fixation material	-
Housing Color	White
Optical cover finish	Microprismatic lens
Overall length	595 mm
Overall width	595 mm
Overall height	70 mm
Dimensions (Height x Width x Depth)	70 x 595 x 595 mm
Compatible ceiling or ceiling installation accessory type	Visible profile ceiling version
Ingress protection code	IP20/44 [Finger-protected; wire-protected, splash-proof]
Mech. impact protection code	IK02 [0.2 J standard]
Safety device	SC [Safety cable]
Net Weight (Piece)	2.350 kg

### Emergency Operation

Central Emergency	No
-------------------	----

### Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
----------------	-----------------------------------

Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
Photobiological risk specification	0.2 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-10 to +35 °C

### Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Initial chromaticity	(0.38, 0.38) SDCM ≤3
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)


Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L85
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L75

### Product Data

Order product name	RC132V G6 43S/840 WIA W60L60 OC
Full product name	RC132V G6 43S/840 WIA W60L60 OC
Full product code	872016975002999
Order code	75002999
Material Nr. (12NC)	911401802487
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169750029
Numerator - Packs per outer box	4
EAN/UPC - Case	8720169750319

# CoreLine Panel gen6

## Dimensional drawing



## Photometric data



Polar Normal (separate) - null - 911401802487

