



Essential Smartbright LED Batten

BN017C LED30/857 2ft

Essential Smartbright LED Batten, 30 W, 3000 lm, 5700 K, Wide beam

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. This new batten range of LED products can be used to replace traditional battens with fluorescent lamps. The process of selecting, installing and maintaining is so easy – it’s a simple switch

Product data

General Information	
Number of gear units	1 unit
Gear	-
Driver included	Yes
Light source engine type	LED
Value ladder	Value
Warranty period	1 years
Light Technical	
Luminous Flux	3,000 lm
Correlated Color Temperature (Nom)	5700 K
Luminous Efficacy (rated) (Nom)	100 lm/W
Color rendering index (CRI)	80
Number of light sources	1
Beam angle of light source	110 degree(s)
Light source color	857 daylight

Optic type	Wide beam
Luminaire light beam spread	110°
Unified glare rating CEN	30
Operating and Electrical	
Input Voltage	220 V
Line Frequency	60 Hz
Inrush current	29 A
Inrush time	0.28 ms
Power Consumption	30 W
Power Factor (Fraction)	0.5
Connection	Flying leads/wires
Cable	Cable 0.3 m without plug
Number of products on MCB of 16 A type B	17
Suitable for random switching	Not applicable

Essential Smartbright LED Batten

Protection class IEC	Safety class II
----------------------	-----------------

Controls and Dimming

Dimmable	-
Control interface	-
Maximum dim level	Not applicable


Mechanical and Housing

Housing Material	Polypropylene
Reflector material	-
Optic material	Polypropylene
Optical cover material	Polypropylene
Housing Color	White
Mounting device	Mounting bracket
Optical cover finish	Opal
Overall length	560 mm
Overall width	60 mm
Overall height	50 mm
Dimensions (Height x Width x Depth)	50 x 60 x 560 mm
Ingress protection code	IP20 [No protection]
Mech. impact protection code	IK03 [0.3 J]
Optical cover type	Opal
Net Weight (Piece)	0.240 kg

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces

Dimensional drawing



CE mark	No
ENEC mark	-
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
Photobiological risk specification	0.2 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.33, 0.34) SDCM<7
Power consumption tolerance	+/-10%

Product Data

Order product name	BN017C LED30/857 2ft
Full product name	BN017C LED30/857 2ft
Full product code	872016975108899
Order code	911401806087
Material Nr. (12NC)	911401806087
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169751088
Numerator - Packs per outer box	30
EAN/UPC - Case	8720169751149

Essential Smartbright LED Batten

