



Ledinaire batten BN045C

BN045C 48S/840 PSU L1200

Ledinaire batten BN045C, 40 W, L1200 mm, 4800 lm, 4000 K, IP20, TW1-ready

L1200 mm, Steel, White, Signal white (RAL9003), Power supply unit (On/Off), 4800 lm, 40 W, 120 lm/W, 4000 K, (0.38, 0.38) SDCM \leq 5, Beam angle 120°, Polycarbonate, IP20 | Finger-protected, IK02 | 0.2 J standard, Safety class I, Push-in connector 3-pole, Simple Connection and removable cover available for feed-through wiring 1-phase (internal wiring is not included)

Product data

General Information		Optic type	
Light source replaceable	No	Beam angle 120°	
Number of gear units	1 unit	Luminaire light beam spread	120°
Driver included	Yes	Unified glare rating CEN	28
Service tag	No	Operating and Electrical	
Lighting Technology	LED	Input Voltage	220-240 V
Value ladder	Value	Line Frequency	50 or 60 Hz
Warranty period	5 years	Inrush current	10.1 A
Light Technical		Inrush time	0.528 ms
Luminous Flux	4,800 lm	Power Consumption	40 W
Saturated Red (R9)	<50	Power Factor (Fraction)	0.9
Correlated Color Temperature (Nom)	4000 K	Connection	Push-in connector 3-pole
Luminous Efficacy (rated) (Nom)	120 lm/W	Cable	-
Color rendering index (CRI)	>80	Number of products on MCB of 16 A type B	14
Light source color	840 neutral white	Suitable for random switching	Yes
		Protection class IEC	Safety class I

Ledinaire batten BN045C

Feed-through wiring	Simple Connection and removable cover available for feed-through wiring 1-phase (internal wiring is not included)
----------------------------	---

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Steel
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	White
Optical cover finish	-
Overall length	1,125 mm
Overall width	58 mm
Overall height	59 mm
Dimensions (Height x Width x Depth)	59 x 58 x 1125 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Net Weight (Piece)	0.900 kg

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	-
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
Photobiological risk specification	0,2 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	1,6
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
--------------------------------	--------

Initial chromaticity	(0.38, 0.38) SDCM≤5
Power consumption tolerance	+/-10%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤5

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	7.5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L70

Sustainability Data

Sustainability rating	Unclassified
Repair class	Repair Class D, this product is not designed to be repaired.
Embedded carbon (A1-A3)	9.28 kg CO ₂ e
Product non-virgin material ratio	22.9 %
Recyclable content ratio of the finished product	62.2 %
GWP total B6 (kg CO₂eq) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO ₂ eq / kWh)
GWP total B6 (kg CO₂eq) Functional Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * 1000 (lm) /lumen output (lm) Declared Unit * 35000 (hrs) * Energy mix (kg CO ₂ eq / kWh)
Non-virgin material ratio of the packaging	Cardboard > 80% recycled Plastic >35% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80% Plastic recycling rate > 40%
Packaging Material	Cardboard Plastic

Product Data

Order product name	BN045C 48S/840 PSU L1200
Full product name	BN045C 48S/840 PSU L1200
Full product code	871951496359799
Order code	911401806485
Material Nr. (12NC)	911401806485
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514963597
Numerator - Packs per outer box	12
EAN/UPC - Case	8719514963658

Ledinaire batten BN045C

Dimensional drawing

