

RC159Z SMB W60L60

911401807787



Accessory, White

Surface-mounted brackets provide a robust and efficient solution for installing recessed luminaires directly onto solid ceilings where suspended or modular ceiling systems are unavailable. Designed to support a wide range of recessed luminaires, the brackets allow for neat and professional surface installations without compromising system quality or visual integration. Their precise mechanical interface ensures secure attachment and ample internal space for wiring, allowing installers to achieve a neat and seamless finish.

Compatible with multiple luminaire families—including SlimBlend, CoreLine Panel Gen6, CoreLine Recessed and Ledinaire Panel Gen5—the brackets offer a flexible approach to project design by enabling the use of recessed luminaires in environments where ceiling integration is not possible. This reduces the need for additional luminaire variants and helps minimise stock complexity. Engineered for installer convenience, the brackets feature a straightforward mounting process that supports fast installation while ensuring reliable long term performance. By enabling simple conversion from recessed to surface mounted application, Surface Mounted Brackets increase design versatility for specifiers and installers alike. Always refer to the installation instructions of the relevant luminaire family to confirm compatibility before installation.

Warnings and Safety

- Always consult the installation instructions of both the accessory and the selected luminaire before installation.
- Ensure the ceiling surface is capable of supporting the weight and fastening requirements of the mounted luminaire.
- Installation must be performed by qualified personnel in accordance with local safety regulations and building standards.

Mechanical and Housing

Overall length	615.5 mm
Overall width	615.5 mm
Overall height	78.5 mm
Dimensions (height x width x depth)	79 x 616 x 616 mm
Material	Aluminium
Ingress protection code	-
Mech. impact protection code	-
Accessory colour	White
Net Weight (Piece)	0.980 kg


Product Data

Order product name	RC159Z SMB W60L60
Full product name	RC159Z SMB W60L60
Full EOC	872016975214699
Order code	911401807787
Material no. (12 NC)	911401807787
Numerator – quantity per pack	1
EAN/UPC — Product/Case	8720169752146
Numerator – packs per outer box	10
EAN/UPC - Case	8720169752214

Approval and Application

CE mark	Yes
EU RoHS compliant	Yes

Dimensional drawing



Related Documents

Documents and certificates	Document Name	Download
Installation Instructions	RC159Z-SMB-Installation-instruction.PDF	Download 
Tender text	Tender_Text_911401807787_en_GB.txt	Download 