



# Essential SmartBright G5 LED Floodlight

## BVC150 LED150/WW PSU 150W SWB G3 GM

Essential SmartBright G5 LED Floodlight, 14100 lm, 150 W, 830 warm white, 110°, Safety class I, Mounting bracket

The Essential SmartBright G5 LED Floodlight is the new successor with robust die-cast aluminum housing suitable for general outdoor application. Lightweight, with a robust die-cast aluminum housing and corrosion-proof coating, it's suitable for general outdoor applications. Plus, with a higher efficacy than the previous generation, it also saves more energy.

### Product data

General Information		Optic type	
Number of gear units	1 unit	Optic type	Wide beam
Gear	-	Luminaire light beam spread	110°
Driver included	Yes	Effective projected area	0.09 m²
Light source engine type	LED	Operating and Electrical	
Value ladder	Value	Input Voltage	220 to 240 V
Warranty period	2 years	Line Frequency	50 or 60 Hz
Light Technical		Inrush current	10 A
Luminous Flux	14,100 lm	Inrush time	0.03 ms
Correlated Color Temperature (Nom)	3000 K	Power Consumption	150 W
Luminous Efficacy (rated) (Nom)	94 lm/W	Power Factor (Fraction)	0.9
Color rendering index (CRI)	80	Connection	Flying leads/wires
Number of light sources	1	Cable	Cable 0.7 m without plug
Beam angle of light source	110 degree(s)	Number of products on MCB of 16 A type B	15
Light source color	830 warm white	Suitable for random switching	No

# Essential SmartBright G5 LED Floodlight

Protection class IEC	Safety class I
----------------------	----------------

## Controls and Dimming

Dimmable	No
Control interface	-
Maximum dim level	Not applicable


## Mechanical and Housing

Housing Material	Aluminum die-cast
Reflector material	Polycarbonate
Optic material	Glass
Optical cover material	Glass
Housing Color	Black
Mounting device	Mounting bracket
Optical cover finish	Clear
Overall length	387 mm
Overall width	315 mm
Overall height	39 mm
Dimensions (Height x Width x Depth)	39 x 315 x 387 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Optical cover type	Tempered glass
Net Weight (Piece)	2.400 kg

## Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces

## Dimensional drawing



CE mark	No
ENEC mark	-
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
Photobiological risk specification	0.2 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-40 to +50 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.44, 0.40) SDCM≤6
Power consumption tolerance	+/-10%

## Product Data

Order product name	BVC150 LED150/WW PSU 150W SWB G3 GM
Full product name	BVC150 LED150/WW PSU 150W SWB G3 GM
Full product code	872016952200899
Order code	911401817386
Material Nr. (12NC)	911401817386
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169522008
Numerator - Packs per outer box	6
EAN/UPC - Case	8720169522244

## Essential SmartBright G5 LED Floodlight

