



Essential Smartbright LED Batten

BN068C LED6/CW L600 TH G2

Essential Smartbright LED Batten, 6.5 W, 600 lm, 6500 K, Wide beam

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. This new batten range of LED products can be used to replace traditional battens with fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch

Product data

General Information		Luminaire light beam spread	
Light source replaceable	No		140°
Number of gear units	1 unit	Operating and Electrical	
Driver included	Yes	Input Voltage	220 to 240 V
Light source engine type	LED	Line Frequency	50 to 60 Hz
Value ladder	Value	Power Consumption	6.5 W
Warranty period	1 years	Power Factor (Fraction)	0.5
Light Technical		Connection	Flying leads/wires
Luminous Flux	600 lm	Cable	Cable without plug 2-pole
Correlated Color Temperature (Nom)	6500 K	Number of products on MCB of 16 A type B	10
Luminous Efficacy (rated) (Nom)	92 lm/W	Protection class IEC	Safety class II
Color rendering index (CRI)	>80	Controls and Dimming	
Light source color	Cool white	Dimmable	No
Optic type	Wide beam	Driver/power unit/transformer	Power supply unit (On/Off)
		Control interface	-

Essential Smartbright LED Batten

Constant light output	No
Maximum dim level	Not applicable

Mechanical and Housing

Housing Material	Polyamide
Optic material	Polycarbonate
Optical cover material	Polyamide
Fixation material	Steel
Housing Color	White
Optical cover finish	Clear
Overall length	585 mm
Overall width	21 mm
Overall height	34.2 mm
Dimensions (Height x Width x Depth)	34 x 21 x 585 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK00 [No protection]
Optical cover type	Polycarbonate linear
Net Weight (Piece)	0.087 kg

Approval and Application

Glow-wire test	Temperature 850 °C, duration 5 s
CE mark	No
EU RoHS compliant	Yes

Ambient temperature range	-20 to +40 °C
---------------------------	---------------

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<7
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Median useful life L70B50	20,000 hour(s)
---------------------------	----------------

Product Data

Order product name	BN068C LED6/CW L600 TH G2
Full product name	BN068C LED6/CW L600 TH G2
Full product code	911401820597
Order code	911401820597
Material Nr. (12NC)	911401820597
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163310596
Numerator - Packs per outer box	24
EAN/UPC - Case	8710163310893

Dimensional drawing

