



Essential Smartbright waterproof

WT035C LED30/CW PSU GM CFW L1200

Essential Smartbright waterproof, 30 W, 3000 lm, 6500 K, 120°

Essential Smartbright slim waterproof

Product data

General Information		Electrical	
Light source replaceable	No	Inrush current	4 A
Number of gear units	1 unit	Inrush time	0.1 ms
Driver included	Yes	Power Consumption	30 W
Light source engine type	LED	Power Factor (Fraction)	0.9
Value ladder	Value	Connection	Connection unit 2-pole
Warranty period	2 years	Cable	Cable 0.25m without plug
		Number of products on MCB of 16 A type B	24
		Protection class IEC	Safety class II
Light Technical		Controls and Dimming	
Luminous Flux	3,000 lm	Dimmable	No
Correlated Color Temperature (Nom)	6500 K	Driver/power unit/transformer	Power supply unit (On/Off)
Luminous Efficacy (rated) (Nom)	90 lm/W	Control interface	-
Color rendering index (CRI)	>70	Constant light output	No
Beam angle of light source	120 degree(s)	Maximum dim level	Not applicable
Light source color	865 cool daylight	Mechanical and Housing	
Optic type	Beam angle 120°	Housing Material	Polycarbonate
Luminaire light beam spread	120°	Reflector material	Steel
Operating and Electrical		Optic material	Polycarbonate
Input Voltage	220 to 240 V	Optical cover material	Polycarbonate
Line Frequency	50 or 60 Hz		

Essential Smartbright waterproof

Fixation material	-
Housing Color	White
Optical cover finish	Opal
Overall length	1,198 mm
Overall width	35.5 mm
Overall height	44.5 mm
Dimensions (Height x Width x Depth)	45 x 36 x 1198 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Optical cover type	Polycarbonate bowl/cover
Net Weight (Piece)	0.290 kg

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	-
CE mark	Yes
ENEC mark	-
EU RoHS compliant	No
Ambient temperature range	-20 °C to 40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Initial chromaticity	0.323 ; 0.35
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.004 %
Median useful life L70B50	20,000 hour(s)
Median useful life L80B50	15,610 hour(s)
Median useful life L90B50	7,330 hour(s)

Product Data

Order product name	WT035C LED30/CW PSU GM CFW L1200
Full product name	WT035C LED30/CW PSU GM CFW L1200
Full product code	871016334404199
Order code	911401821380
Material Nr. (12NC)	911401821380
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163344041
Numerator - Packs per outer box	24
EAN/UPC - Case	8710163344102

Dimensional drawing

