



Essential SmartBright G5 LED Floodlight

BVC150 LED30/CW PSU 30W SWB G3 GM

Essential SmartBright G5 LED Floodlight, 3000 lm, 30 W, 865 cool daylight, 110°, Safety class I, Mounting bracket

The Essential SmartBright G5 LED Floodlight is the new successor with robust die-cast aluminum housing suitable for general outdoor application. Lightweight, with a robust die-cast aluminum housing and corrosion-proof coating, it's suitable for general outdoor applications. Plus, with a higher efficacy than the previous generation, it also saves more energy.

Product data

General Information		Optic type	
Number of gear units	1 unit	Optic type	Wide beam
Gear	-	Luminaire light beam spread	110°
Driver included	Yes	Effective projected area	0.02 m ²
Light source engine type	LED	Operating and Electrical	
Value ladder	Value	Input Voltage	220 to 240 V
Warranty period	2 years	Line Frequency	50 or 60 Hz
Light Technical		Inrush current	3 A
Luminous Flux	3,000 lm	Inrush time	0.03 ms
Correlated Color Temperature (Nom)	6500 K	Power Consumption	30 W
Luminous Efficacy (rated) (Nom)	100 lm/W	Power Factor (Fraction)	0.9
Color rendering index (CRI)	80	Connection	Flying leads/wires
Number of light sources	1	Cable	Cable 0.7 m without plug
Beam angle of light source	110 degree(s)	Number of products on MCB of 16 A type B	72
Light source color	865 cool daylight	Suitable for random switching	No

Essential SmartBright G5 LED Floodlight

Protection class IEC	Safety class I
Controls and Dimming	
Dimmable	No
Control interface	-
Maximum dim level	Not applicable
Mechanical and Housing	
Housing Material	Aluminum die-cast
Reflector material	Polycarbonate
Optic material	Glass
Optical cover material	Glass
Housing Color	Black
Mounting device	Mounting bracket
Optical cover finish	Clear
Overall length	193 mm
Overall width	156 mm
Overall height	26 mm
Dimensions (Height x Width x Depth)	26 x 156 x 193 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Optical cover type	Tempered glass
Net Weight (Piece)	0.460 kg
Approval and Application	
Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces

CE mark	No
ENEC mark	-
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
Photobiological risk specification	0.2 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-40 to +50 °C


Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.31, 0.34) SDCM≤6
Power consumption tolerance	+/-10%

Product Data

Order product name	BVC150 LED30/CW PSU 30W SWB G3 GM
Full product name	BVC150 LED30/CW PSU 30W SWB G3 GM
Full product code	872016952188999
Order code	911401833386
Material Nr. (12NC)	911401833386
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169521889
Numerator - Packs per outer box	24
EAN/UPC - Case	8720169522121

Dimensional drawing



Essential SmartBright G5 LED Floodlight

