



CoreLine Batten

BN126C LED52S/840 PSU L1500

CoreLine Batten, 37 W, L1500 mm, 5200 lm, 4000 K, Opal, IP20/40, TW1-ready, EL-ready

L1500 mm, Steel, White, Signal white (RAL9003), Power supply unit (On/Off), 5200 lm, 37 W, 130 lm/W, 4000 K, (0.38, 0.38) SDCM≤3, Beam angle 120°, Opal, Polycarbonate, IP20/40 | Finger-protected;Wire-protected, IK04 | 0.5 J standard plus, Safety class I, Push-in connector 3-pole, Simple Connection and removable cover available for feed-through wiring 1-phase (internal wiring is not included), Self-contained emergency lighting is possible when used with a compatible battery kit accessory

Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void

Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes
Lighting Technology	LED
Value ladder	Performance
Warranty period	5 years

Light Technical	
Luminous Flux	5,200 lm
Saturated Red (R9)	<50
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	130 lm/W
Color rendering index (CRI)	>80
Light source color	840 neutral white
Optic type	Beam angle 120°
Luminaire light beam spread	120°

CoreLine Batten

Unified glare rating CEN	26
--------------------------	----

Operating and Electrical

Input Voltage	220–240 V
Line Frequency	50 or 60 Hz
Inrush current	10.6 A
Inrush time	0.527 ms
Power Consumption	37 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 3-pole
Cable	–
Number of products on MCB of 16 A type B	13
Suitable for random switching	Not applicable
Protection class IEC	Safety class I
Feed-through wiring	Simple Connection and removable cover available for feed-through wiring 1-phase (internal wiring is not included)

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	–
Constant light output	No

Mechanical and Housing

Housing Material	Steel
Reflector material	–
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	–
Housing Color	White
Optical cover finish	Opal
Overall length	1,450 mm
Overall width	65 mm
Overall height	65 mm
Dimensions (Height x Width x Depth)	65 x 65 x 1450 mm
Ingress protection code	IP20/40 [Finger-protected;Wire-protected]
Mech. impact protection code	IK04 [0.5 J standard plus]
Net Weight (Piece)	1.040 kg

Emergency Operation

Central Emergency	No
Emergency lighting	Self-contained emergency lighting is possible when used with a compatible battery kit accessory

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes

ENEC mark	ENEC mark
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
Photobiological risk specification	0.2 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Flickering value (PstLM) – Flickering value 1 as per EN 61000-3-3	
Stroboscopic effect visibility measure (SVM)	1.6
Ambient temperature range	–20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM≤3
Power consumption tolerance	+/-10%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤3

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L80

Sustainability Data

Sustainability rating	Unclassified
Repair class	Repair Class D, this product is not designed to be repaired.
Embedded carbon (A1-A3)	15 kg CO ₂ e
Product non-virgin material ratio	23.5 %
Recyclable content ratio of the finished product	66.1 %
GWP total B6 (kg CO ₂ eq) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO ₂ eq / kwh)
GWP total B6 (kg CO ₂ eq) Functional Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * 1000 (lm) / lumen output (lm) Declared Unit * 35000 (hrs) * Energy mix (kg CO ₂ eq / kwh)
Non-virgin material ratio of the packaging	Cardboard > 80% recycled Plastic >35% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80% Plastic recycling rate > 40%
Packaging Material	Cardboard Plastic

Product Data


Order product name	BN126C LED52S/840 PSU L1500
Full product name	BN126C LED52S/840 PSU L1500
Full product code	871951494884699
Order code	94884699

CoreLine Batten


Material Nr. (12NC)	911401834584
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514948846
Numerator - Packs per outer box	6

EAN/UPC - Case	8719514949065
----------------	---------------

Dimensional drawing



Photometric data



Polar Normal (separate) - 911401834584

