



# CoreLine Batten

## BN126C LED48S/830 PSU L1500

CoreLine Batten, 40 W, L1500 mm, 4800 lm, 3000 K, Opal, IP20, TW1-ready

The CoreLine Batten delivers on the CoreLine promise of innovative, easy-to-use and high-quality luminaires. The efficient design makes installation quick and easy, enabling seamless light-line creation without additional accessories. CoreLine Batten provides universal light distribution, supporting homogeneous illuminance and visual comfort. Interact Ready luminaires with integrated wireless communications are also available, for use with Interact gateways, sensors and software.

### Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void

### Product data

General Information		Sustainability rating	
Light source replaceable	No	Unclassified	
Number of gear units	1 unit	Light Technical	
Driver included	Yes	Luminous Flux	4,800 lm
Service tag	Yes	Saturated Red (R9)	<50
Lighting Technology	LED	Correlated Color Temperature (Nom)	3000 K
Value ladder	Performance	Luminous Efficacy (rated) (Nom)	120 lm/W
Serviceability class	Class C, luminaire without serviceable parts, not serviceable	Color rendering index (CRI)	>80
Warranty period	5 years	Light source color	830 warm white
		Optic type	Beam angle 120°

## CoreLine Batten

Luminaire light beam spread	120°
Unified glare rating CEN	26

### Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Inrush current	10.6 A
Inrush time	0.527 ms
Power Consumption	40 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 3-pole
Cable	-
Number of products on MCB of 16 A type B	13
Suitable for random switching	Not applicable
Protection class IEC	Safety class I
Feed-through wiring	Simple Connection and removable cover available for feed-through wiring 1-phase (internal wiring is not included)

### Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

### Mechanical and Housing

Housing Material	Steel
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	White
Optical cover finish	Opal
Overall length	1,450 mm
Overall width	65 mm
Overall height	65 mm
Dimensions (Height x Width x Depth)	65 x 65 x 1450 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK04 [0.5 J standard plus]
Net Weight (Piece)	1.360 kg

### Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
----------------	-----------------------------------

Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
Photobiological risk specification	0.2 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	1.6
Ambient temperature range	-20 to +40 °C

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM≤3
Power consumption tolerance	+/-10%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤3

### Over Time Performance (IEC Compliant)


Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L80
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 75000 h	L80

### Product Data


Order product name	BN126C LED48S/830 PSU L1500
Full product name	BN126C LED48S/830 PSU L1500
Full product code	871951494885399
Order code	911401834684
Material Nr. (12NC)	911401834684
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514948853
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514949072

# CoreLine Batten

## Dimensional drawing



## Photometric data



Polar Normal (separate) - null - 911401834684

