



CoreLine Batten

BN126C LED100S/840 PSU L1800

CoreLine Batten, 75 W, L1800 mm, 10000 lm, 4000 K, Opal, IP20, TW1-ready

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Batten range of LED products can be used to replace traditional battens with fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void

Product data

General Information		Light Technical	
Light source replaceable	No	Luminous Flux	10,000 lm
Number of gear units	1 unit	Saturated Red (R9)	<50
Driver included	Yes	Correlated Color Temperature (Nom)	4000 K
Service tag	Yes	Luminous Efficacy (rated) (Nom)	130 lm/W
Lighting Technology	LED	Color rendering index (CRI)	>80
Value ladder	Performance	Light source color	840 neutral white
Serviceability class	Class C, luminaire without serviceable parts, not serviceable	Optic type	Beam angle 120°
Warranty period	5 years	Luminaire light beam spread	120°
Sustainability rating	Unclassified	Unified glare rating CEN	26

CoreLine Batten

Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Inrush current	17.6 A
Inrush time	0.832 ms
Power Consumption	75 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 3-pole
Cable	-
Number of products on MCB of 16 A type B	7
Suitable for random switching	Not applicable
Protection class IEC	Safety class I
Feed-through wiring	Simple Connection and removable cover available for feed-through wiring 1-phase (internal wiring is not included)

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing	
Housing Material	Steel
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	White
Optical cover finish	Opal
Overall length	1,750 mm
Overall width	65 mm
Overall height	65 mm
Dimensions (Height x Width x Depth)	65 x 65 x 1750 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK04 [0.5 J standard plus]
Net Weight (Piece)	1.610 kg

Approval and Application	
Glow-wire test	Temperature 650 °C, duration 30 s

Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
Photobiological risk specification	0.2 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	1.6
Ambient temperature range	-20 to +40 °C


Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM≤3
Power consumption tolerance	+/-10%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤3

Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L80


Product Data	
Order product name	BN126C LED100S/840 PSU L1800
Full product name	BN126C LED100S/840 PSU L1800
Full product code	871951494890799
Order code	94890799
Material Nr. (12NC)	911401835184
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514948907
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514949126

CoreLine Batten

Dimensional drawing



Photometric data



Polar Normal (separate) - null - 911401835184

