



SmartBright G3 LED Floodlight

BVP151 LED300/NW PSU 250W SWB G3 GM

SmartBright G3 LED Floodlight, 30000 lm, 250 W, 840 neutral white, 110°, Safety class I, Mounting bracket adjustable

The SmartBright G3 LED Floodlight is the new successor with robust die-cast aluminum housing suitable for general outdoor application. It delivers high efficacy and outstanding energy savings.

Product data

General Information		Effective projected area	
Number of gear units	1 unit		0.134 m ²
Gear	EB [Electronic]	Operating and Electrical	
Driver included	Yes	Line Frequency	50 or 60 Hz
Light source engine type	LED	Inrush current	115 A
Value ladder	Value	Inrush time	0.15 ms
		Power Consumption	250 W
		Power Factor (Fraction)	0.9
		Connection	Flying leads/wires
		Cable	Cable 1.0 m without plug 3-pole
		Number of products on MCB of 16 A type B	10
		Suitable for random switching	No
		Protection class IEC	Safety class I
		Controls and Dimming	
		Dimmable	-
		Control interface	-
Light Technical			
Luminous Flux	30,000 lm		
Correlated Color Temperature (Nom)	4000 K		
Luminous Efficacy (rated) (Nom)	120 lm/W		
Color rendering index (CRI)	80		
Number of light sources	1		
Beam angle of light source	110 degree(s)		
Light source color	840 neutral white		
Optic type	Symmetric 110°		
Luminaire light beam spread	110°		

SmartBright G3 LED Floodlight

Maximum dim level	Not applicable
Mechanical and Housing	
Housing Material	Aluminum die-cast
Reflector material	Polycarbonate
Optic material	Glass
Optical cover material	Tempered glass
Housing Color	Grey
Mounting device	Mounting bracket adjustable
Optical cover finish	Clear
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [6 J]
Optical cover type	Tempered glass
Net Weight (Piece)	4.800 kg
Approval and Application	
Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	No
ENEC mark	-
Photobiological risk	Photobiological risk group 1 @200mm to EN62778

EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-25 °C to 50 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Initial chromaticity	(0.380,0.380) SDCM \leq 5
Power consumption tolerance	+/-10%

Product Data

Order product name	BVP151 LED300/NW PSU 250W SWB G3 GM
Full product name	BVP151 LED300/NW PSU 250W SWB G3 GM
Full product code	872016976352499
Order code	911401839187
Material Nr. (12NC)	911401839187
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169763524
Numerator - Packs per outer box	4
EAN/UPC - Case	8720169763548

Dimensional drawing

