



# CoreLine Fastset, surface-mounted

## SM155C 30\_48S/830\_840 PSU TW3 PI5 L1160

CoreLine Fastset, surface-mounted, All-in, 34 W, 30 W, 25 W, 20 W, L1160 mm, 3000 lm, 3450 lm, 4100 lm, 4800 lm, 3000 K, 4000 K

L1160 mm, Steel, White, Signal white (RAL9003), Power supply unit (On/Off), All-in, Multi Lumen, All-in, Multi Color Temperature, 3000 lm, 3450 lm, 4100 lm, 4800 lm, 34 W, 30 W, 25 W, 20 W, 150 lm/W, 140 lm/W, 3000 K, 4000 K, (0.38,0.38)SDCM<3; (0.44,0.40)SDCM<3, Opal, Opal, Polycarbonate, IP20/44 | Finger-protected; wire-protected, splash-proof, IK06 | 1 J, Safety class I, Push-in connector 5-pole, Feed-through wiring 3-phase

### Product data

General Information	
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes
Value ladder	Performance
Warranty period	5 years
Light Technical	
Luminous Flux	3,000 3,450 4,100 4,800 lm
Saturated Red (R9)	<50
Correlated Color Temperature (Nom)	3000 4000 K
Luminous Efficacy (rated) (Nom)	150 140 lm/W
Color rendering index (CRI)	>80

Light source color	-
Optic type	Opal
Luminaire light beam spread	110°
Unified glare rating CEN	25
All-in Type	All-in, Multi Lumen All-in, Multi Color Temperature
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Inrush current	17 A
Inrush time	0.14 ms
Power Consumption	34 30 25 20 W

## CoreLine Fastset, surface-mounted

Power Factor (Fraction)	0.95
Connection	Push-in connector 5-pole
Cable	-
Number of products on MCB of 16 A type B	25
Suitable for random switching	No
Protection class IEC	Safety class I
Feed-through wiring	Feed-through wiring 3-phase
Total harmonic distortion	20 %

### Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Maximum dim level	Not applicable

### Mechanical and Housing

Housing Material	Steel
Reflector material	Steel
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	White
Optical cover finish	Opal
Overall length	1,160 mm
Overall width	163 mm
Overall height	67 mm
Dimensions (Height x Width x Depth)	67 x 163 x 1160 mm
Ingress protection code	IP20/44 [Finger-protected; wire-protected, splash-proof]
Mech. impact protection code	IK06 [1 J]
Net Weight (Piece)	2.500 kg

### Emergency Operation

Central Emergency	No
-------------------	----

### Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Photobiological risk	Photobiological risk group 0 @ 200mm to EN62471
Photobiological risk specification	0.2 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1

Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-20 °C to 45 °C

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38,0.38)SDCM<3;(0.44,0.40)SDCM<3
Power consumption tolerance	+/-10%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤3

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L80
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L65 L70

### Sustainability Data

Sustainability rating	Unclassified
Repair class	Repair Class D, this product is not designed to be repaired.
Embedded carbon (A1-A3)	81.4 kg CO <sub>2e</sub>
Product non-virgin material ratio	13.2 %
Recyclable content ratio of the finished product	44.1 %
GWP total B6 (kg CO <sub>2eq</sub> ) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO <sub>2eq</sub> / kwh)
GWP total B6 (kg CO <sub>2eq</sub> ) Functional Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * 1000 (lm) / lumen output (lm) Declared Unit * 35000 (hrs) * Energy mix (kg CO <sub>2</sub> eq / kwh)

### Product Data


Order product name	SM155C 30_48S/830_840 PSU TW3 P15 L1160
Full product name	SM155C 30_48S/830_840 PSU TW3 P15 L1160
Full product code	872016951016699
Order code	51016699
Material Nr. (12NC)	911401841485
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169510166
Numerator - Packs per outer box	4
EAN/UPC - Case	8720169510241

# CoreLine Fastset, surface-mounted

## Dimensional drawing



## Photometric data



Polar Normal (separate) - 911401841485

