



Ledinaire Batten

BN021C LED10S/840 L600

Ledinaire Batten, 10 W, L600 mm, 1050 lm, 1050 lm, 4000 K, Opal, IP20, TW1-ready

L600 mm, Polycarbonate, White, Power supply unit (On/Off), 1050 lm, 1050 lm, 10 W, 105 lm/W, 4000 K, 0.38, 0.38, SDCM \leq 5, Very wide beam, Opal, Polycarbonate, IP20 | Finger-protected, IK02 | 0.2 J standard, Safety class II, Plug-in connector 2-pole, Simple connection and removable cover available for feed-through wiring 1-phase (internal wiring is not included)

Product data

General Information		Unified Glare Rating (CEN)	
Light source replaceable	No	27	
Number of gear units	Unit	Operating and Electrical	
Driver included	Yes	Input Voltage	220 to 240 V
Lighting Technology	LED	Line Frequency	50 or 60 Hz
Value ladder	Value	Inrush current	9 A
Warranty period	5 years	Inrush time	0.001 ms
Light Technical		Power Consumption	10 W
Luminous Flux	1,050 1,050 lm	Power Factor (Fraction)	0.9
Saturated Red (R9)	<50	Connection	Plug-in connector 2-pole
Correlated Colour Temperature (Nom)	4000 K	Cable	-
Luminous efficacy (rated) (nom.)	105 lm/W	Number of products on MCB (16 A type B)	10
Colour rendering index (CRI)	>80	Suitable for random switching	Not applicable
Light source colour	840 neutral white	Protection class IEC	Safety class II
Optic type	Very wide beam	Feed-through wiring	Simple connection and removable cover available for feed-through wiring 1-phase (internal wiring is not included)
Luminaire light beam spread	170°		

Ledinaire Batten

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Maximum dim level	Not applicable

Mechanical and Housing	
Housing material	Polycarbonate
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	-
Housing Colour	White
Optical cover/lens finish	Opal
Overall length	586 mm
Overall width	28.4 mm
Overall height	35.7 mm
Dimensions (height x width x depth)	36 x 28 x 586 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Net Weight (Piece)	0.090 kg

Approval and Application	
Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	-
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
Photobiological risk specification	0.2 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	0.38, 0.38, SDCM≤5
Power consumption tolerance	+/-10%

Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤5
--	--------

Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50,000 h	7.5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L65

Sustainability Data	
Sustainability rating	Unclassified
Repair class	Repair Class D, this product is not designed to be repaired.
Embedded carbon (A1-A3)	2.28 kg CO ₂ e
Product non-virgin material ratio	11.8 %
Recyclable the content ratio of the finished product	51.2 %
GWP total B6 (kg CO ₂ eq) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO ₂ eq / kwh)
GWP total B6 (kg CO ₂ eq) Functional Unit	Please calculate using your local energy mix value: POWER DECLARED UNIT (kW) * 1000 (lm) / LUMEN OUTPUT DECLARED UNIT (lm) * 35000 (hrs) * ENERGY MIX (kg CO ₂ eq / kwh)

Product Data	
Order product name	BN021C LED10S/840 L600
Full product name	BN021C LED10S/840 L600
Full EOC	871951452786799
Order code	911401841982
Material no. (12 NC)	911401841982
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514527867
Numerator – packs per outer box	40
EAN/UPC – Case	8719514527966

Ledinaire Batten

Dimensional drawing

