



Ledinaire Batten

BN021C LED15S/840 L900

Ledinaire Batten, 15 W, L900 mm, 1600 lm, 1600 lm, 4000 K, Opal, IP20, TW1-ready

Uncomplicated, off-the-shelf quality and reliability – that’s the beauty of LEDINAIRE. LEDINAIRE keeps it simple, delivering the essentials and nothing more. We don’t spend money on things you don’t need: no flashy packaging, no unnecessary brochures. We offer a selection of popular, low-cost LED solutions, ensuring that LED lighting is within your price range, and that our products always meet the highest possible standard. This no-nonsense approach to lighting means that you get exactly what it says on the box – reliability, affordability, and energy efficiency. Designed for general lighting and cove lighting applications, the slim LEDINAIRE BN060C Batten is a cost-effective energy-saving LED solution. It is also extremely flexible, offering a choice of two light outputs plus the option of installation in a light-line.

Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Lighting Technology	LED
Value ladder	Value
Serviceability class	Class C, luminaire without serviceable parts, not serviceable
Warranty period	5 years
Sustainability rating	Unclassified

Light Technical	
Luminous Flux	1,600 1,600 lm
Saturated Red (R9)	<50
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	107 lm/W
Color rendering index (CRI)	>80
Light source color	840 neutral white
Optic type	Very wide beam
Luminaire light beam spread	168°
Unified glare rating CEN	27

Ledinaire Batten

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Inrush current	11 A
Inrush time	0.001 ms
Power Consumption	15 W
Power Factor (Fraction)	0.9
Connection	Plug-in connector 2-pole
Cable	-
Number of products on MCB of 16 A type B	10
Suitable for random switching	Not applicable
Protection class IEC	Safety class II
Feed-through wiring	Simple Connection and removable cover available for feed-through wiring 1-phase (internal wiring is not included)

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Maximum dim level	Not applicable

Mechanical and Housing	
Housing Material	Polycarbonate
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	White
Optical cover finish	Opal
Overall length	886 mm
Overall width	28.4 mm
Overall height	35.7 mm
Dimensions (Height x Width x Depth)	36 x 28 x 886 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Net Weight (Piece)	0.130 kg

Approval and Application	
Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	-
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
Photobiological risk specification	0.2 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	0.38, 0.38, SDCM≤5
Power consumption tolerance	+/-10%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤5

Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50000 h	7.5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L65

Product Data	
Order product name	BN021C LED15S/840 L900
Full product name	BN021C LED15S/840 L900
Full product code	871951452788199
Order code	52788199
Material Nr. (12NC)	911401842182
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514527881
Numerator - Packs per outer box	40
EAN/UPC - Case	8719514527980

Ledinaire Batten

Dimensional drawing

