



Ledinaire Batten

BN021C LED20S/840 L1200

Ledinaire Batten, 20 W, L1200 mm, 2100 lm, 2100 lm, 4000 K, Opal, IP20, TW1-ready

The Ledinaire batten (BN021C) range contains a selection of popular off-the-shelf batten LED luminaires that come with Philips high-quality levels at a competitive price. Reliable, energy-efficient and affordable. Ledinaire enables, simple and flexible installation, with a light-line creation option.

Product data

General Information	
Light source replaceable	No
Number of gear units	Unit
Driver included	Yes
Lighting Technology	LED
Value ladder	Value
Serviceability class	Class C, luminaire without serviceable parts, not serviceable
Warranty period	5 years
Sustainability rating	Unclassified
Light Technical	
Luminous Flux	2,100 2,100 lm
Saturated Red (R9)	<50
Correlated Colour Temperature (Nom)	4000 K
Luminous efficacy (rated) (nom.)	105 lm/W
Colour rendering index (CRI)	>80
Light source colour	840 neutral white
Optic type	Very wide beam

Luminaire light beam spread	174°
Unified Glare Rating (CEN)	27
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Inrush current	14.3 A
Inrush time	0.001 ms
Power Consumption	20 W
Power Factor (Fraction)	0.9
Connection	Plug-in connector 2-pole
Cable	-
Number of products on MCB (16 A type B)	10
Suitable for random switching	Not applicable
Protection class IEC	Safety class II
Feed-through wiring	Simple connection and removable cover available for feed-through wiring 1-phase (internal wiring is not included)

Ledinaire Batten

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Maximum dim level	Not applicable

Mechanical and Housing

Housing material	Polycarbonate
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	-
Housing Colour	White
Optical cover/lens finish	Opal
Overall length	1,186 mm
Overall width	28.4 mm
Overall height	35.7 mm
Dimensions (height x width x depth)	36 x 28 x 1186 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Net Weight (Piece)	0.160 kg

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	-
Photobiological risk	Photobiological risk group 0 @200mm to EN62778

Photobiological risk specification	0.2 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	0.38, 0.38, SDCM≤5
Power consumption tolerance	+/-10%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤5


Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	7.5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L65

Product Data

Order product name	BN021C LED20S/840 L1200
Full product name	BN021C LED20S/840 L1200
Full EOC	871951452790499
Order code	911401842382
Material no. (12 NC)	911401842382
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514527904
Numerator – packs per outer box	40
EAN/UPC – Case	8719514528000

Dimensional drawing



Ledinaire Batten

