

BN021C LED19S/830
L1200

911401842482



Ledinaire Batten, 20 W, L1200 mm, 1900 lm, 3000 K, Opal, IP20, TW1-ready

L1200 mm, Polycarbonate, White, Power supply unit (On/Off), 1900 lm, 20 W, 95 lm/W, 3000 K, 0.43, 0.40, SDCM≤5, Very wide beam, Opal, Polycarbonate, IP20 | Finger-protected, IK02 | 0.2 J standard, Safety class II, Plug-in connector 2-pole, Simple connection and removable cover available for feed-through wiring 1-phase (internal wiring is not included)

General Information

Light source replaceable	No
Number of gear units	Unit
Driver included	Yes
Service Tag	No
Lighting Technology	LED
Value ladder	Value
Warranty period	5 years

Light Technical

Luminous Flux	1,900 lm
Saturated Red (R9)	<50
Correlated Colour Temperature (Nom)	3000 K
Luminous efficacy (rated) (nom.)	95 lm/W
Colour rendering index (CRI)	>80
Light source colour	830 warm white
Optic type	Very wide beam
Luminaire light beam spread	174°
Unified Glare Rating (CEN)	27

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Inrush current	14.3 A
Inrush time	0.001 ms
Power Consumption	20 W
Power Factor (Fraction)	0.9
Connection	Plug-in connector 2-pole
Cable	-
Number of products on MCB (16 A type B)	10
Suitable for random switching	Not applicable
Protection class IEC	Safety class II
Feed-through wiring	Simple connection and removable cover available for feed-through wiring 1-phase (internal wiring is not included)

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Maximum dim level	Not applicable

Mechanical and Housing

Housing material	Polycarbonate
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	-
Housing Colour	White
Optical cover/lens finish	Opal
Overall length	1,186 mm
Overall width	28.4 mm
Overall height	35.7 mm
Dimensions (height x width x depth)	36 x 28 x 1186 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2] standard]
Net Weight (Piece)	0.160 kg

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	-
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
Photobiological risk specification	0.2 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	0.43, 0.40, SDCM≤5
Power consumption tolerance	+/-10%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤5

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	7.5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L65

Sustainability Data


Sustainability rating	Unclassified
Repair class	Repair Class D, this product is not designed to be repaired.
Embedded carbon (A1-A3)	3.71 kg CO ₂ e
Product non-virgin material ratio	12.4 %
Recyclable the content ratio of the finished product	48.3 %
GWP total B6 (kg CO ₂ eq) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO ₂ eq / kwh)
GWP total B6 (kg CO ₂ eq) Functional Unit	Please calculate using your local energy mix value: POWER DECLARED UNIT (kW) * 1000 (lm) / LUMEN OUTPUT DECLARED UNIT (lm) * 35000 (hrs) * ENERGY MIX (kg CO ₂ eq / kwh)

Product Data

Order product name	BN021C LED19S/830 L1200
Full product name	BN021C LED19S/830 L1200
Full EOC	871951452791199
Order code	911401842482

Material no. (12 NC)	911401842482
Numerator – quantity per pack	1
EAN/UPC — Product/Case	8719514527911
Numerator – packs per outer box	40
EAN/UPC - Case	8719514528017

Dimensional drawing



Related Documents

Documents and certificates	Document Name	Download
Environmental Product Declaration	EPD-Philips-Ledinaire-batten-BN021C-LED19S-830-L1200-911401842482.pdf	Download 
Installation Instructions	BN021C EU-MI-0427_Final v3.pdf	Download 

