



Ledinaire Batten

BN021C LED25S/840 L1500

Ledinaire Batten, 24 W, L1500 mm, 2600 lm, 2600 lm, 4000 K, Opal, IP20, TW1-ready

L1500 mm, Polycarbonate, White, Power supply unit (On/Off), 2600 lm, 2600 lm, 24 W, 108 lm/W, 4000 K, 0.38, 0.38, SDCM≤5, Very wide beam, Opal, Polycarbonate, IP20 | Finger-protected, IK02 | 0.2 J standard, Safety class II, Plug-in connector 2-pole, Simple Connection and removable cover available for feed-through wiring 1-phase (internal wiring is not included)

Product data

General Information		Unified glare rating CEN	
Light source replaceable	No	Unified glare rating CEN	27
Number of gear units	1 unit	Operating and Electrical	
Driver included	Yes	Input Voltage	220 to 240 V
Service tag	No	Line Frequency	50 or 60 Hz
Lighting Technology	LED	Inrush current	16.8 A
Value ladder	Value	Inrush time	0.001 ms
Warranty period	5 years	Power Consumption	24 W
Light Technical		Power Factor (Fraction)	0.9
Luminous Flux	2,600 2,600 lm	Connection	Plug-in connector 2-pole
Saturated Red (R9)	<50	Cable	-
Correlated Color Temperature (Nom)	4000 K	Number of products on MCB of 16 A type B	10
Luminous Efficacy (rated) (Nom)	108 lm/W	Suitable for random switching	Not applicable
Color rendering index (CRI)	>80	Protection class IEC	Safety class II
Light source color	840 neutral white	Feed-through wiring	Simple Connection and removable cover available for feed-through wiring 1-phase (internal wiring is not included)
Optic type	Very wide beam		
Luminaire light beam spread	168°		

Ledinaire Batten

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Maximum dim level	Not applicable

Mechanical and Housing

Housing Material	Polycarbonate
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	White
Optical cover finish	Opal
Overall length	1,486 mm
Overall width	28.4 mm
Overall height	35.7 mm
Dimensions (Height x Width x Depth)	36 x 28 x 1486 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Net Weight (Piece)	0.210 kg

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	-
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
Photobiological risk specification	0.2 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	0.38, 0.38, SDCM≤5
Power consumption tolerance	+/-10%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤5

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	7.5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L65

Sustainability Data

Sustainability rating	Unclassified
Repair class	Repair Class D, this product is not designed to be repaired.
Embedded carbon (A1-A3)	4.52 kg CO ₂ e
Product non-virgin material ratio	13.5 %
Recyclable content ratio of the finished product	48.4 %
GWP total B6 (kg CO ₂ eq) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO ₂ eq / kwh)
GWP total B6 (kg CO ₂ eq) Functional Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * 1000 (lm) / lumen output (lm) Declared Unit * 35000 (hrs) * Energy mix (kg CO ₂ eq / kwh)
Non-virgin material ratio of the packaging	Cardboard > 80% recycled Plastic >35% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80% Plastic recycling rate > 40%
Packaging Material	Cardboard Plastic

Product Data

Order product name	BN021C LED25S/840 L1500
Full product name	BN021C LED25S/840 L1500
Full product code	871951452792899
Order code	911401842582
Material Nr. (12NC)	911401842582
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514527928
Numerator - Packs per outer box	40
EAN/UPC - Case	8719514528024

Ledinaire Batten

Dimensional drawing

