



SmartBright Select LED Batten

BN158C LED8/SCCT L600 AU

SmartBright Select LED Batten, 6.5 W, 750 lm, Selectable, Opal

SmartBright Select LED Batten BN158C provides flexibility to customers. There are 3 CCTs in one batten and 4 different sizes, based on their specific need.

Product data

General Information		Operating and Electrical	
Number of gear units	1 unit	Input Voltage	220 to 240 V
Gear	-	Line Frequency	50 or 60 Hz
Driver included	Yes	Inrush current	3.47 A
Light source engine type	LED	Inrush time	0.124 ms
Value ladder	Value	Power Consumption	6.5 W
Warranty period	3 years	Power Factor (Fraction)	0.9
		Connection	Mains outlet socket
		Cable	-
		Number of products on MCB of 16 A type B	211
		Suitable for random switching	Yes
		Protection class IEC	Safety class II
		Controls and Dimming	
		Dimmable	No
		Control interface	-
		Maximum dim level	Not applicable
		Mechanical and Housing	
		Housing Material	Polycarbonate

SmartBright Select LED Batten

Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	White RAL 9003
Mounting device	Mounting bracket
Optical cover finish	Opal
Overall length	585 mm
Overall width	20 mm
Overall height	32 mm
Dimensions (Height x Width x Depth)	32 x 20 x 585 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Optical cover type	Polycarbonate
Net Weight (Piece)	0.180 kg

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	No
ENEC mark	-
Photobiological risk	Photobiological risk group 0 @ 200mm to EN62471

Photobiological risk specification	0.2 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Initial chromaticity	(0.44, 0.40) SDCM \leq 6
Power consumption tolerance	+/-10%

Product Data

Order product name	BN158C LED8/SCCT L600 AU
Full product name	BN158C LED8/SCCT L600 AU
Full product code	872016951034099
Order code	911401842685
Material Nr. (12NC)	911401842685
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169510340
Numerator - Packs per outer box	12
EAN/UPC - Case	8720169510463

