



SmartBright Solar All-in-two Street Light

BRP216 LED30/740 G2 Solar

External high efficiency polysilicon solar panel Die-casting aluminum housing, Professional lighting distribution, 2000, 3000, 4000lumens versions available, Plug-play connector between luminaire and PV panel Inbuilt LiFePO4 battery and MPPT controller.

Warnings and Safety

- Install the luminaire in a sunny place that is not shaded by trees, buildings and walls, then the solar panel can receive the maximum sunlight for charging the battery.
- Charge the product under sunlight for at least 8 hours before first time using.
- This luminaire does not need any external electrical connection.
- It works 100% on solar energy.

Product data

General Information		Battery voltage	
Driver included	Yes	Battery voltage	3.2 V
Value ladder	Value	Panel type	Poly crystalline
Warranty period	3 years	Panel voltage	16 V
Light Technical		Panel peak wattage	40 W
Luminous Flux	3,000 lm	Grid connection type	Off grid
Correlated Color Temperature (Nom)	4000 K	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	180 lm/W	Dimmable	No
Color rendering index (CRI)	70	Configurability	Not configurable
Operating and Electrical		Solar dimming profile	Pre-configured
Battery type	Lithium Ferro Phosphate	Mechanical and Housing	
Battery ampere hour	75 Ah	Housing Color	Gray
		Overall length	583 mm

SmartBright Solar All-in-two Street Light

Overall width	218 mm
Overall height	96 mm
Dimensions (Height x Width x Depth)	96 x 218 x 583 mm
Material	Die-casting Aluminum
Battery location	In built
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Optical cover type	Polycarbonate
Net Weight (Piece)	7.300 kg

Approval and Application

Ambient temperature range	0 °C to 50 °C
---------------------------	---------------

Over Time Performance (IEC Compliant)

Median useful life L70B50	50,000 hour(s)
---------------------------	----------------

Application Conditions

Ambient temperature range for charging	0 °C to 50 °C
--	---------------

Ambient temperature range for discharging (when light is on)	-10 °C to 60 °C
--	-----------------

Product Data

Order product name	BRP216 LED30/740 G2 Solar
Full product name	BRP216 LED30/740 G2 Solar
Full product code	692382866149600
Order code	911401845202
Material Nr. (12NC)	911401845202
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828661496
Numerator - Packs per outer box	1
EAN/UPC - Case	6923828661496

Dimensional drawing

