



# SmartBright Plus Panel

## RC048B+ LED34S/840 PSU W60L60

SmartBright Plus Panel, 120 lm/W, 840 neutral white

The Philips SmartBright Plus panel (RC048B+) range features a selection of popular off-the-shelf LED luminaires that come with Philips high quality levels at a competitive price. Reliable, high energy efficient and affordable, this latest generation of SmartBright Plus LED panel lights are designed for diffuse, comfortable lighting in a wide range of general lighting applications. Our range of SmartBright Plus panel lighting is also available with accessories for easy installation on different types of ceilings – just what you need.

### Product data

General Information		Optic type	
Number of gear units	1 unit		Beam angle 120°
Gear	-	Luminaire light beam spread	120°
Driver included	Yes	Effective projected area	0.354 m <sup>2</sup>
Light source engine type	LED	Operating and Electrical	
Value ladder	Value	Input Voltage	220 to 240 V
Warranty period	3 years	Line Frequency	50 or 60 Hz
Light Technical		Inrush current	16 A
Luminous Flux	3,400 lm	Inrush time	0.2 ms
Correlated Color Temperature (Nom)	4000 K	Power Consumption	28 W
Luminous Efficacy (rated) (Nom)	120 lm/W	Power Factor (Fraction)	0.9
Color rendering index (CRI)	80	Connection	Push-in connector 2-pole
Beam angle of light source	120 degree(s)	Cable	-
Light source color	840 neutral white	Number of products on MCB of 16 A type B	19
		Suitable for random switching	Yes

# SmartBright Plus Panel

Protection class IEC	Safety class II
----------------------	-----------------

## Controls and Dimming

Dimmable	No
Control interface	-
Maximum dim level	Not applicable

## Mechanical and Housing

Housing Material	Steel
Reflector material	Acrylate
Optic material	Polystyrene
Optical cover material	Acrylate
Housing Color	White RAL 9003
Mounting device	-
Optical cover finish	Opal
Overall length	595 mm
Overall width	595 mm
Overall height	59 mm
Dimensions (Height x Width x Depth)	59 x 595 x 595 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Optical cover type	Opal
Net Weight (Piece)	1.290 kg

## Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces

CE mark	Yes
ENEC mark	-
Photobiological risk	Photobiological risk group 0 @ 200mm to EN62471
Photobiological risk specification	0.2 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-10 to +35 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Initial chromaticity	(0.38, 0.38) SDCM $\leq$ 5
Power consumption tolerance	+/-10%

## Product Data

Order product name	RC048B+ LED34S/840 PSU W60L60
Full product name	RC048B+ LED34S/840 PSU W60L60
Full product code	872016951212299
Order code	911401846885
Material Nr. (12NC)	911401846885
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169512122
Numerator - Packs per outer box	6
EAN/UPC - Case	8720169512122

