

SB Waterproof WT068 G2

Mechanical and Housing

Housing Material	Polycarbonate
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Grey
Mounting device	Surface & Suspended (Asymmetric/ Symmetric)
Optical cover finish	Opal
Overall length	595 mm
Overall width	65.2 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Optical cover type	Opal
Net Weight (Piece)	0.300 kg

Approval and Application

Glow-wire test	Temperature 850 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	-
Photobiological risk	Photobiological risk group 0 @200mm to EN62778

Photobiological risk specification	0.2 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-20 to +45 °C


Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Initial chromaticity	(x=0.31,y=0.33)SDCM≤5
Power consumption tolerance	+/-10%

Product Data

Order product name	WT068C CW LED18 L600 PSU G2
Full product name	WT068C CW LED18 L600 PSU G2
Full product code	872016951441699
Order code	51441699
Material Nr. (12NC)	911401862685
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169514416
Numerator - Packs per outer box	12
EAN/UPC - Case	8720169514539

Dimensional drawing



WT068C L600

