



CoreLine tubular waterproof

WT210Z SW2

CoreLine tubular waterproof, Accessory, Steel

CoreLine Tubular Waterproof delivers on the CoreLine promise of innovative, easy-to-use and high-quality luminaires. A reliable, efficient luminaire with a very long lifetime, CoreLine Tubular Waterproof comes in two versions to meet various applications needs. The ammonia-resistant and sealed luminaire (PMMA tube) is suitable for animal lighting, livestock and food applications, while the PC version offers a modern and industrial design that is suitable for a wide range of general lighting applications. Both versions come with significant dust, water and impact protection, making them relevant for specific applications. CoreLine Tubular Waterproof WT210C luminaires promise energy savings and less maintenance. At the same time, they can be installed in next to no time and without tools, thanks to pre-installed through-wiring and an external connector, which mean the luminaire does not require opening. These waterproof lighting solutions are flexible to mount on ceilings or suspended in both indoor and outdoor environments.

Product data

General Information		Mechanical and Housing	
Value ladder	Performance	Overall height	1,000 mm
		Overall diameter	15 mm
		Material	Stainless steel
Operating and Electrical		Ingress protection code	-
Input Voltage	- V	Mech. impact protection code	-
Line Frequency	- Hz	Accessory color	Steel
Protection class IEC	-	Net Weight (Piece)	0.080 kg

CoreLine tubular waterproof

Approval and Application

CE mark	Yes
EU RoHS compliant	Yes

Sustainability Data

Non-virgin material ratio of the packaging	Cardboard > 80% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80%
Packaging Material	Cardboard

Product Data

Order product name	WT210Z SW2
--------------------	------------

Full product name	WT210Z SW2
Full product code	871951495610099
Order code	911401867784
Material Nr. (12NC)	911401867784
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514956100
Numerator - Packs per outer box	100
EAN/UPC - Case	8719514956124

Dimensional drawing

