



StreetStar Gen2

BRP241 LED40/WW 30W DMO PSU

StreetStar Gen2, 4000 lm, 30 W, 730 warm white, Safety class I, Side-entry for diameter 48 to 60 mm

StreetStar Gen2 brings great value for street lighting with its energy-efficient, cost-effective, slim but robust design. It's the perfect option for municipalities and businesses seeking a reliable and sustainable lighting solution. StreetStar Gen2 offers unparalleled value and performance.

Product data

| General Information | | Power Factor (Fraction) | |
|------------------------------------|----------------------|-------------------------|-------------------------------------|
| Gear | EB [Electronic] | | 0.95 |
| Driver included | Yes | Connection | Flying leads/wires |
| Light source engine type | LED | Cable | Cable without plug 3-pole |
| Value ladder | Value | Protection class IEC | Safety class I |
| Light Technical | | Controls and Dimming | |
| Luminous Flux | 4,000 lm | Dimmable | Fixed |
| Correlated Color Temperature (Nom) | 3000 K | Control interface | - |
| Luminous Efficacy (rated) (Nom) | 135 lm/W | Maximum dim level | Not applicable |
| Color rendering index (CRI) | ≥70 | Mechanical and Housing | |
| Light source color | 730 warm white | Housing Material | Aluminum die-cast |
| Effective projected area | 0.052 m ² | Reflector material | Polycarbonate |
| | | Optic material | Polycarbonate |
| Operating and Electrical | | Optical cover material | Glass |
| Input Voltage | 220 to 240 V | Housing Color | RAL7040 |
| Line Frequency | 50 or 60 Hz | Mounting device | Side-entry for diameter 48 to 60 mm |
| Inrush current | 28 A | Optical cover finish | Clear |
| Power Consumption | 30 W | Overall length | 455 mm |

StreetStar Gen2

| | |
|-------------------------------------|--|
| Overall width | 135 mm |
| Overall height | 81 mm |
| Dimensions (Height x Width x Depth) | 81 x 135 x 455 mm |
| Ingress protection code | IP66 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code | IK08 [6 J] |
| Optical cover type | Tempered glass |
| Net Weight (Piece) | 1.450 kg |

Approval and Application

| | |
|------------------------------------|---------------|
| Flammability mark | - |
| CE mark | Yes |
| ENEC mark | - |
| EU RoHS compliant | Yes |
| Performance ambient temperature Tq | 35 °C |
| Ambient temperature range | -40 to +50 °C |

Initial Performance (IEC Compliant)

| | |
|-------------------------|--------|
| Luminous flux tolerance | +/-10% |
|-------------------------|--------|

| | |
|-----------------------------|--------------------|
| Initial chromaticity | (0.33,0.40) SDCM<5 |
| Power consumption tolerance | +/-10% |

Product Data

| | |
|---------------------------------|-----------------------------|
| Order product name | BRP241 LED40/WW 30W DMO PSU |
| Full product name | BRP241 LED40/WW 30W DMO PSU |
| Full product code | 872110330411700 |
| Order code | 911401867887 |
| Material Nr. (12NC) | 911401867887 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8721103304117 |
| Numerator - Packs per outer box | 1 |
| EAN/UPC - Case | 8721103304117 |

Dimensional drawing

