



Ledinaire All-in floodlights

BVP167 LED12/830_40_65 PSU 10W SWB

Ledinaire All-in floodlights, 10 W, 1100 lm, 1200 lm, 3000 K, 4000 K, 6500 K, CRI80, Symmetrical, IP65

With this Ledinaire all-in floodlights range, you can easily adjust the color temperature by a simple switch. No need to choose between warm white, neutral white or cool white anymore, you get all these in one single product! The range comes with the Philips high quality levels at a competitive price. Reliable, energy-efficient and affordable – just what you need.

Product data

General Information		Colour rendering index (CRI)	
Lamp family code	LED12S [LED module, system flux 1200 lm]	Colour rendering index (CRI)	>80
Number of gear units	Unit	Light source colour	Multi Colour Temperature
Driver included	Yes	Optic type	Symmetric 110°
Light source engine type	LED system in flux	Luminaire light beam spread	110°
Value ladder	Value	Optic type outdoor	Symmetrical
Serviceability class	Class C, luminaire without serviceable parts, not serviceable	All-in Type	All-in, Multi Color Temperature
Warranty period	5 years	Effective projected area	0.006300000000000001 m²
Sustainability rating	Unclassified	Operating and Electrical	
		Input Voltage	220-240 V
		Line Frequency	50 or 60 Hz
		Inrush current	0.78 A
		Inrush time	0.00648 ms
		Power Consumption	10 W
		Power Factor (Fraction)	0.95
		Connection	Flying leads/cables
Light Technical			
Upwards light output ratio	0		
Luminous Flux	1,100 1,200 lm		
Correlated Colour Temperature (Nom)	3000 4000 6500 K		
Luminous efficacy (rated) (nom.)	120 110 lm/W		

Ledinaire All-in floodlights

Cable	Cable 1.0 m without plug
Number of products on MCB (16 A type B)	218
Suitable for random switching	Not applicable
Protection class IEC	Safety class I
Surge Protection (Common/Differential)	Surge protection level until 1.5 kV differential mode and 1.5 kV common mode
Total harmonic distortion	20 %

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Driver integrated on LED board (DoB)
Control interface	-
Constant light output	No
Embedded control	-
Photocell	-

Mechanical and Housing

Housing material	Aluminium die cast
Reflector material	Polycarbonate
Optic material	Glass
Optical cover/lens material	Tempered glass
Fixation material	Steel
Housing Colour	Grey
Mounting device	Via U Shaped Bracket, Aiming Scale Angle, Universal Installation
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Overall length	130 mm
Overall width	85 mm
Overall height	31 mm
Dimensions (height x width x depth)	31 x 85 x 130 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Standard tilt angle post-top	27°
Standard tilt angle side entry	-
Optical cover type	Glass
Net Weight (Piece)	0.250 kg

Emergency Operation

Central Emergency	No
-------------------	----

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
----------------	-----------------------------------

Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	-
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
Photobiological risk specification	0.2 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Flickering value (PstLM)	1
Ambient temperature range	-25 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.440,0.403); (0.369,0.364); (0.313,0.337) SDCM<5
Power consumption tolerance	+/-10%
Init. Colour Rendering Index Tolerance	-2
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤5

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	7.5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L80
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 75000 h	L70

Product Data

Order product name	BVP167 LED12/830_40_65 PSU 10W SWB
Full product name	BVP167 LED12/830_40_65 PSU 10W SWB
Full EOC	872016973601699
Order code	911401871386
Material no. (12 NC)	911401871386
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8720169736016
Numerator – packs per outer box	24
EAN/UPC - Case	8720169736207

Ledinaire All-in floodlights

Dimensional drawing

