



# Ledinaire Waterproof

## WT060C LED56S/840 PSU L1500 BN

Ledinaire Waterproof, (in brown Eco Packaging), 46 W, L1500 mm, 5600 lm, 4000 K, Symmetrical, Opal, IP66, IK08

The Ledinaire waterproof (WT060) range contains a selection of popular off-the-shelf waterproof LED luminaires that comes with the high Philips quality levels at a competitive price. Reliable, energy efficient and affordable. Ledinaire enables, simple and quick installation, with optional through wiring possibility.

### Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Service tag	No
Lighting Technology	LED
Value ladder	Value
Serviceability class	Class C, luminaire without serviceable parts, not serviceable
Warranty period	5 years
Sustainability rating	Unclassified

Light Technical	
Luminous Flux	5,600 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	121 121 lm/W
Color rendering index (CRI)	>80
Beam angle of light source	120 degree(s)
Light source color	840 neutral white

Optic type	Symmetrical
Luminaire light beam spread	120°
Unified glare rating CEN	26

Sustainability Data	
Embedded carbon (A1-A3)	18.3 kg CO <sub>2</sub> e
Recyclable content ratio of the finished product	51.6 %
Product non-virgin material ratio	9.4 %
GWP total B6 (kg CO <sub>2</sub> eq) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO <sub>2</sub> eq / kwh)
GWP total B6 (kg CO <sub>2</sub> eq) Functional Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * 1000 (lm) /lumen output (lm) Declared Unit * 35000 (hrs) * Energy mix (kg CO <sub>2</sub> eq / kwh)

## Ledinaire Waterproof

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Inrush current	3.6 A
Inrush time	0.122 ms
Power Consumption	46 W
Power Factor (Fraction)	0.9
Connection	Connection unit 2-pole
Cable	-
Number of products on MCB of 16 A type B	40
Suitable for random switching	Yes
Protection class IEC	Safety class II
Total harmonic distortion	20 %

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Maximum dim level	Not applicable

Mechanical and Housing	
Housing Material	Polycarbonate
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Stainless steel
Housing Color	Grey
Optical cover finish	Opal
Overall length	1,501 mm
Overall width	69 mm
Overall height	59 mm
Dimensions (Height x Width x Depth)	59 x 69 x 1501 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Net Weight (Piece)	0.700 kg

Approval and Application	
Glow-wire test	Temperature 850 °C, duration 30 s

Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	-
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	1.6
Ambient temperature range	-20 to +45 °C

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	<5
Power consumption tolerance	+/-10%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤5


Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50000 h	7.5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L70
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 75000 h	-

Product Data	
Order product name	WT060C LED56S/840 PSU L1500 BN
Full product name	WT060C LED56S/840 PSU L1500 BN
Full product code	871016336011999
Order code	911401876880
Material Nr. (12NC)	911401876880
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163360119
Numerator - Packs per outer box	12
EAN/UPC - Case	8710163360232

# Ledinaire Waterproof

## Dimensional drawing

WT060C



Strip type	A	B	C	D	E	F	G
L800	88	88	88	871	100 100	100 100	
L1200	88	88	88	1200	200 200	200 200	
L1500	88	88	88	1500	100 100	100 100	
L1800	88	88	88	1800	100 200	100 200	88x2

