



Ledinaire Floodlights Solar

BVP085 LED17/830

Ledinaire Floodlights Solar, 13 W, 1690 lm, 3000 K, CRI80, IR remote, Symmetrical, IP65

Install it everywhere, no energy bill anymore. This Ledinaire floodlight range is powered by a solar panel and an integrated battery. A remote control enables you to light it On/Off and choose between different lighting durations and dimming possibilities. The range comes with the Philips high quality levels at a competitive price. Reliable, energy-efficient and affordable – just what you need.

Warnings and Safety

- The floodlight will not work and the battery will not charge below 0°C in order to protect the battery lifetime
- Optimum battery charging under bright sun exposure
- Disposal at end of life: Battery to be removed by professional

Product data

| General Information | |
|---------------------------|--|
| Lamp family code | LED17S [LED module, system flux 1700 lm] |
| Number of gear units | 1 unit |
| Driver included | Yes |
| Light source engine type | LED system in flux |
| Value ladder | Value |
| Warranty period | 2 years |
| Light Technical | |
| Upward light output ratio | 0 |

| | |
|------------------------------------|----------------|
| Luminous Flux | 1690 lm |
| Saturated Red (R9) | <50 |
| Correlated Color Temperature (Nom) | 3000 K |
| Luminous Efficacy (rated) (Nom) | 140 lm/W |
| Color rendering index (CRI) | >80 |
| Beam angle of light source | 114 degree(s) |
| Light source color | 830 warm white |
| Optic type | Very wide beam |
| Luminaire light beam spread | 114° |
| Optic type outdoor | Symmetrical |

Ledinaire Floodlights Solar

| | |
|--------------------------|---------------------|
| Effective projected area | 0.04 m ² |
|--------------------------|---------------------|

Operating and Electrical

| | |
|--|--|
| Input Voltage | 3 V |
| Line Frequency | 0 Hz |
| Inrush current | 0 A |
| Inrush time | 0 ms |
| Power Consumption | 13 W |
| Power Factor (Fraction) | 1 |
| Connection | Waterproof External plug-in connector 3-pole |
| Cable | 2x0.75mm ² |
| Number of products on MCB of 16 A type B | - |
| Suitable for random switching | Not applicable |
| Protection class IEC | Safety class III |
| Surge Protection (Common/Differential) | Surge protection level until 1.5 kV differential mode and 1.5 kV common mode |
| Feed-through wiring | - |

Controls and Dimming

| | |
|-------------------------------|--------------------------------------|
| Dimmable | Yes |
| Driver/power unit/transformer | Driver integrated on LED board (DoB) |
| Control interface | IR remote |
| Constant light output | No |
| Maximum dim level | 10% |
| Embedded control | Solar dim profile version 1 |

Mechanical and Housing

| | |
|-------------------------------------|---|
| Housing Material | Aluminum |
| Reflector material | Polycarbonate |
| Optic material | Polycarbonate |
| Optical cover material | Glass |
| Fixation material | Steel |
| Housing Color | Grey |
| Mounting device | Via U Shaped Bracket, Aiming Scale Angle, Universal Installation |
| Optical cover shape | Flat |
| Optical cover finish | Clear |
| Reflector Finish | High-gloss reflector |
| Overall length | 220 mm |
| Overall width | 232 mm |
| Overall height | 60.4 mm |
| Dimensions (Height x Width x Depth) | 60 x 232 x 220 mm |
| Ingress protection code | IP65 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code | IK06 [1 J] |
| Explosion hazard class | - |
| Standard tilt angle posttop | 27° |
| Standard tilt angle side entry | - |

| | |
|--------------------|----------|
| Mounting | Wall |
| Optical cover type | Glass |
| Net Weight (Piece) | 2.830 kg |

Emergency Operation

| | |
|-------------------|----|
| Central Emergency | No |
|-------------------|----|

Approval and Application

| | |
|------------------------------------|--|
| Glow-wire test | Temperature 650 °C, duration 30 s |
| Flammability mark | For mounting on normally flammable surfaces |
| CE mark | Yes |
| ENEC mark | - |
| Photobiological risk | Photobiological risk group 0 @200mm to EN62778 |
| EU RoHS compliant | Yes |
| Performance ambient temperature Tq | 25 °C |
| Ambient temperature range | 0 to +50 °C |

Initial Performance (IEC Compliant)

| | |
|---------------------------------------|-----------------------|
| Luminous flux tolerance | +/-10% |
| Initial chromaticity | (0.313,0.334) SDCM<=5 |
| Power consumption tolerance | +/-5% |
| Init. Color Rendering Index Tolerance | -2 |

Over Time Performance (IEC Compliant)

| | |
|---|-------|
| Control gear failure rate at median useful life 50000 h | 7.5 % |
| Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 35000 h | L65 |
| Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h | L70 |

Sustainability Data

| | |
|-----------------------|--|
| Sustainability rating | Unclassified |
| Repair class | Repair Class D, this product is not designed to be repaired. |

Product Data

| | |
|---------------------------------|------------------|
| Order product name | BVP085 LED17/830 |
| Full product name | BVP085 LED17/830 |
| Full product code | 872016975199699 |
| Order code | 911401881702 |
| Material Nr. (12NC) | 911401881702 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8720169751996 |
| Numerator - Packs per outer box | 5 |
| EAN/UPC - Case | 8720169752078 |

Ledinaire Floodlights Solar

Dimensional drawing

