



Ledinaire Floodlights Solar, 32 W, 4480 lm, 4000 K, CRI80, IR remote, Symmetrical, IP65

Aluminum, Grey, Single layer powder coating, Driver integrated on LED board (DoB), Solar dim profile version 1, 4480 lm, 32 W, 140 lm/W, 4000 K, (0.312,0.334) SDCM $\leq$ 5, CRI80, Symmetrical, IP65 | Dust penetration-protected, jet-proof, IK06 | 1 J, Safety class III, Surge protection level until 1.5 kV differential mode and 1.5 kV common mode, 2 $\times$ 0.75mm², Waterproof External plug-in connector 3-pole

Warnings and Safety

- The floodlight will not work and the battery will not charge below 0°C in order to protect the battery lifetime
- Optimum battery charging under bright sun exposure
- Disposal at end of life: Battery to be removed by professional

General Information

Lamp family code	LED45S [LED Module, system flux 4500 lm]
Number of gear units	1 unit
Driver included	Yes
Light source engine type	LED system in flux
Service tag	No
Value ladder	Value
Warranty period	2 years

Light Technical

Upward light output ratio	0
Luminous Flux	4,480 lm
Saturated Red (R9)	<50
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	140 lm/W
Color rendering index (CRI)	>80
Beam angle of light source	114 degree(s)
Light source color	840 neutral white
Optic type	Very wide beam
Luminaire light beam spread	114°
Optic type outdoor	Symmetrical
Effective projected area	0.09 m²

Operating and Electrical

Input Voltage	10 V
Line Frequency	0 Hz
Inrush current	0 A
Inrush time	0 ms
Power Consumption	32 W
Power Factor (Fraction)	1
Connection	Waterproof External plug-in connector 3-pole
Cable	2×0.75mm²
Number of products on MCB of 16 A type B	-
Suitable for random switching	Not applicable
Protection class IEC	Safety class III
Surge Protection (Common/Differential)	Surge protection level until 1.5 kV differential mode and 1.5 kV common mode
Feed-through wiring	-

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Driver integrated on LED board (DoB)
Control interface	IR remote
Constant light output	No
Maximum dim level	10%
Embedded control	Solar dim profile version 1

Mechanical and Housing

Housing Material	Aluminum
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Glass
Fixation material	Steel
Housing Color	Grey
Mounting device	Via U Shaped Bracket, Aiming Scale Angle, Universal Installation
Optical cover shape	Flat
Optical cover finish	Clear
Reflector Finish	High-gloss reflector
Overall length	320 mm
Overall width	342 mm
Overall height	63.5 mm
Dimensions (Height x Width x Depth)	64 x 342 x 320 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Explosion hazard class	-
Standard tilt angle posttop	27°
Standard tilt angle side entry	-
Mounting	Wall
Optical cover type	Glass
Net Weight (Piece)	6.200 kg

Emergency Operation

Central Emergency	No
-------------------	----

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	-
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	0 to +50 °C


Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.312,0.334) SDCM<=5
Power consumption tolerance	+/-5%
Init. Color Rendering Index Tolerance	-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	7.5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 35000 h	L65
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L70

Dimensional drawing



Sustainability Data

Sustainability rating	Unclassified
Repair class	Repair Class D, this product is not designed to be repaired.
Non-virgin material ratio of the packaging	Cardboard > 80% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80%
Packaging Material	Cardboard

Product Data

Order product name	BVP085 LED45/840
Full product name	BVP085 LED45/840
Full product code	872016975204799
Order code	75204799
Material Nr. (12NC)	911401882202
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169752047
Numerator - Packs per outer box	3
EAN/UPC - Case	8720169752122

Related Documents

Documents and certificates	Document Name	Download
Installation Instructions	MI-BVP085-Ledinaire-Solar-floodlight.pdf	Download 

