



Essential SmartBright Solar Compact

BVS010 LED10/765 Solar

Outdoor solar compact with inbuilt lithium battery and PV panel, inbuilt motion sensor, button switch to change the working modes and LED luminaire integrated in ABS plastic housing.

Warnings and Safety

- Install the luminaire in a sunny place that is not shaded by trees, buildings and walls, then the solar panel can receive the sunlight for charging the battery
- Charge the product under sunlight for 8 hours before first use.

Product data

General Information		Panel peak wattage	
Driver included	Yes	Panel peak wattage	5,5 W
Value ladder	Value	Charge controller type	PWM
		Cable	-
		Grid connection type	Off grid
Light Technical		Controls and Dimming	
Luminous Flux	1,000 lm	Dimmable	Preset Dimming
Correlated Color Temperature (Nom)	6500 K	Configurability	Not configurable
Luminous Efficacy (rated) (Nom)	100 lm/W	Solar dimming profile	Motion sensor dimming
Color rendering index (CRI)	70		
Operating and Electrical		Mechanical and Housing	
Battery type	Li-ion	Housing Color	Black
Battery ampere hour	3 Ah	Overall length	313.9 mm
Battery voltage	7.2 V	Overall width	211.3 mm
Battery charging & discharging cycles	500	Overall height	37.4 mm
Panel type	Mono crystalline	Dimensions (Height x Width x Depth)	37 x 211 x 314 mm
Panel voltage	11 V	Material	Acrylonitrile-butadiene-styrene

Essential SmartBright Solar Compact

Battery location	Inbuilt luminaire
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Optical cover type	Polycarbonate
Net Weight (Piece)	1.310 kg

Approval and Application

CE mark	Yes
Ambient temperature range	0 to +45 °C

Product Data

Order product name	BVS010 LED10/765 Solar
--------------------	------------------------

Full product name	BVS010 LED10/765 Solar
Full product code	872016975823099
Order code	911401886902
Material Nr. (12NC)	911401886902
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169758230
Numerator - Packs per outer box	8
EAN/UPC - Case	8720169758278

Dimensional drawing

