



Essential SmartBright Solar Compact

BVS010 LED10/730 Solar

Outdoor solar compact with inbuilt lithium battery and PV panel, inbuilt motion sensor, button switch to change the working modes and LED luminaire integrated in ABS plastic housing.

Warnings and Safety

- Install the luminaire in a sunny place that is not shaded by trees, buildings and walls, then the solar panel can receive the sunlight for charging the battery
- Charge the product under sunlight for 8 hours before first use.

Product data

General Information		Panel peak wattage	
Driver included	Yes		5,5 W
Value ladder	Value	Charge controller type	PWM
Light Technical		Cable	-
Luminous Flux	1,000 lm	Grid connection type	Off grid
Correlated Color Temperature (Nom)	3000 K	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	100 lm/W	Dimmable	Preset Dimming
Color rendering index (CRI)	70	Configurability	Not configurable
Operating and Electrical		Solar dimming profile	Motion sensor dimming
Battery type	Li-ion	Mechanical and Housing	
Battery ampere hour	3 Ah	Housing Color	Black
Battery voltage	7.2 V	Overall length	313.9 mm
Battery charging & discharging cycles	500	Overall width	211.3 mm
Panel type	Mono crystalline	Overall height	37.4 mm
Panel voltage	11 V	Dimensions (Height x Width x Depth)	37 x 211 x 314 mm
		Material	Acrylonitrile-butadiene-styrene

Essential SmartBright Solar Compact

Battery location	Inbuilt luminaire
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Optical cover type	Polycarbonate
Net Weight (Piece)	1.310 kg

Approval and Application

CE mark	Yes
Ambient temperature range	0 to +45 °C

Product Data

Order product name	BVS010 LED10/730 Solar
--------------------	------------------------

Full product name	BVS010 LED10/730 Solar
Full product code	872016975825499
Order code	75825499
Material Nr. (12NC)	911401887102
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169758254
Numerator - Packs per outer box	8
EAN/UPC - Case	8720169758292

Dimensional drawing

